




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	MAY10/18	L.CHAN
B	UPDATE LAYOUT	JUL.5,2022	L.CHAN



FRONT VIEW




SIDE VIEW



BOTTOM VIEW

R0.25 [R.010]MAX.



RECOMMENDED PANEL CUTOUT

MATERIALS:

PLASTIC HOUSING: ENGINEERING THERMOPLASTIC
FLAMMABILITY RATING UL94V-0, COLOR: BLACK

CONTACTS:

PHOSPHOR BRONZE
PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES
SEE AMPHENOL PART NUMBER FOR DETAIL.
50μ" [1.27 MICRONS] MIN. NICKEL UNDERPLATE.
GOLD FLASH ON CONTACT TAILS.


SHIELD:

COPPER ALLOY PLATING NICKEL

WAVE SOLDERING WITH PEAK TEMPERATURE 260°C FOR 5~8 SECONDS.

PART NUMBER: RJE09-888-AX10

GOLD PLATING:
1= 6μ"
2= 15μ"
3= 30μ"
4= 50μ"



RECOMMENDED P.C.B LAYOUT
(COMPONENT SIDE OF BOARD)
TOLERANCE: ±0.05[.002] (TOP VIEW)

UNLESS SPECIFIED OTHERWISE		DRAWN HANSON.C	DATE MAY10/18	Amphenol Canada Corp. www.amphenolcanada.com	
PRIMARY UNITS INCH		CHECKED L.CHAN	DATE MAY10/18		
SECONDARY MILLIMETER		M.E. APP'D		TITLE RJE09 SERIES MODULAR JACK, 8 PORT, 8 POSITIONS, 8 CONTACTS, SHIELD WITH TOP TABS AND TWO TABS ON EACH SIDES- RoHS COMPLIANT	
REFERENCE IN PARENTHESES		Q.A. APP'D			
GENERAL TOLERANCES		DWG APPR.		DWG. NO. P-RJE09-888-AX10	
1 DECIMAL PLACE ±0.38		ENG. REL. NO.			
2 DECIMAL PLACES ±0.25		REF.		CODE ID NO. 03554 DWG SIZE: C SCALE: N/A SHEET 1 OF 1	
3 DECIMAL PLACES ±0.20		THIRD ANGLE PROJECTION			
ANGULAR DEGREES ±1.0°		DO NOT SCALE DRAWING			