





Note ① The tightening torque of Ref. No. ⑤ : 2 to 2.5 N·m.
Apply Loctite 243 HENKEL JAPAN or equivalent to the threaded portion (M14×0.75) of Ref. No. ① in order to prevent loosening.

3	Polyphenylene sulfide	(Black)	6	Phosphor bronze	Nickel plating					
2	Copper alloy	Silver plating 5μm min.	5	Brass	Nickel plating					
1	Zinc alloy	Matte finish nickel plating	4	Polyphenylene sulfide	(Black)					
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS				
UNITS mm				SCALE 2 : 1		COUNT 1	DESCRIPTION OF REVISIONS DIS-C-00016516	DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI	DATE 20231113
 HIROSE ELECTRIC CO., LTD.				APPROVED : TP. KOMATSU		20230509	DRAWING NO. EDC-006762-81-00			
				CHECKED : HY. KOBAYASHI		20230509	PART NO. RM12BRD-2S(81)			
				DESIGNED : HT. ZENBA		20230509	CODE NO. CL0109-0609-8-81			
				DRAWN : KR. SUZUKI		20230508	 1/1			