

10		9		8		7	
ITEM	MOLEX P/N	DESCRIPTION				QTY	UOM
A	50375083	2.5MM LOW PROFILE HOUSING 526408				1	PC
B	8701039	2.5 Low Profile Crimp Rec Term 5263PBT				8	PC
PL	-	PART IDENTIFICATION LABEL				1	PC

FROM	TO	WIRE SIZE	WIRE TYPE	COLOR
A1	-	22 AWG	UL 1569	BLACK
A2	-	22 AWG	UL 1569	BLACK
A3	-	22 AWG	UL 1569	BLACK
A4	-	22 AWG	UL 1569	BLACK
A5	-	22 AWG	UL 1569	BLACK
A6	-	22 AWG	UL 1569	BLACK
A7	-	22 AWG	UL 1569	BLACK
A8	-	22 AWG	UL 1569	BLACK




TABLE			
FG PART #	L1	L2 (REF)	TITLE
2264311082	150±4	65	Mini-Spox R-S 8ckt 150mm disc Sn
2264311083	300±4	140	Mini-Spox R-S 8ckt 300mm disc Sn
2264311084	600±6	290	Mini-Spox R-S 8ckt 600mm disc Sn

NOTE:

1. CABLE ASSEMBLY MUST PASS 100% CONTINUITY AND POLARITY TEST
2. CONNECTOR VIEW IS SHOWN FROM MATING SIDE
3. LABEL TEXT MUST BE 2MM MAX IN HEIGHT WITH ARIAL FONT AND WRAPPED IN FLAG TYPE ON A SINGLE WIRE.
4. THE PRODUCT HAS TO MEET PERFORMANCE SPECIFICATION AS PER ES-36586-004
5. FREE ENDS MUST BE STRIPPED, TWISTED & TINNED. THE LENGTH OF TINNING IS 5 ± 1 MM. TINNING DIA MUST BE 1 MM MAX.

MOLEX PN
MOLEX
BATCH WK/YR

FUNCTIONAL SYMBOLS <

DOCUMENT STATUS	P1	RELEASE DATE	2024/07/02	04:59:42
-----------------	----	--------------	------------	----------