





Note $\triangle 1$ The tightening torque of Ref. No. $\textcircled{5}$: 2 to 3 N·m.
Apply Loctite 243 HENKEL JAPAN or equivalent to the threaded portion (M14×0.75) of Ref. No. $\textcircled{1}$ in order to prevent loosening.

3	Polyphenylene sulfide	(Black)	6	Phosphor bronze	Nickel plating					
2	Copper alloy	Silver plating 2μm min.	5	Brass	Nickel plating					
1	Zinc alloy	Matte finish nickel plated	4	Polyphenylene sulfide	(Black)					
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS				
UNITS mm				SCALE 2 : 1		COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00015636	DESIGNED HT. ZENBA	CHECKED HY. KOBAYASHI	DATE 20230620
 HIROSE ELECTRIC CO., LTD.				APPROVED : TP. KOMATSU		20230601	DRAWING NO. EDC-027508-81-00			
				CHECKED : HY. KOBAYASHI		20230601	PART NO. RM12BRD-3PH(81)			
				DESIGNED : HT. ZENBA		20230601	CODE NO. CL0109-0824-0-81			
				DRAWN : KR. SUZUKI		20230531	 1 