




Note 1 The tightening torque of Ref. No. ⑤: 2 to 2.5 N·m.
Apply Loctite 243 HENKEL JAPAN or equivalent to the threaded portion (M14×0.75) of Ref. No. ① in order to prevent loosening.

3	Polyphenylene sulfide	(Black)	6	Phosphor bronze	Nickel plating				
2	Copper alloy	Silver plating 2μm min.	5	Brass	Nickel plating				
1	Zinc alloy	Matte finish nickel plated	4	Polyphenylene sulfide	(Black)				
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS			
UNITS mm		SCALE 2 : 1		COUNT 3	DESCRIPTION OF REVISIONS DIS-C-00015636		DESIGNED HT. ZENBA	CHECKED HY. KOBAYASHI	DATE 20230620
HIROSE ELECTRIC CO., LTD.		APPROVED : TP. KOMATSU			20230419		DRAWING NO. EDC-027509-81-00		
		CHECKED : TP. KOMATSU			20230419		PART NO. RM12BRD-4PH(81)		
		DESIGNED : HT. ZENBA			20230419		CODE NO. CL0109-0825-3-81		
		DRAWN : KR. SUZUKI			20230419		1/1		