


Mar.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes 1 Rotation example of Ref. No. ① and ⑤ are shown.
- ② The tightening torque of Ref. No. ⑤: 2 to 3 N·m.
- ③ The tightening torque of Ref. No. ⑧: 0.2 to 0.3 N·m.
Across flats hexagon head of Ref. No. ⑧: 1.27
Apply Loctite 243 HENKEL JAPAN or equivalent to the threaded portion of Ref. No. ⑧ in order to prevent loosening.
- ④ The tightening torque of Ref. No. ⑦: 0.12 to 0.15 N·m.
Apply Loctite 243 HENKEL JAPAN or equivalent to the threaded portion of Ref. No. ⑦ in order to prevent loosening.
- 5 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure, please confirm before the use.

5	Aluminum alloy	Matte finish alumite (chrome)			
4	Brass	Matte finish chrome plate	10	Polyphenylene sulfide	(Black)
3	Polyphenylene sulfide	(Black)	9	Chloroprene rubber	(Black)
2	Brass	Silver plating 4μm min.	8	Steel	Nickel plating
1	Zinc alloy	Matte finish chrome plate	7	Brass	Nickel plating
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
Hexagon socket set screw M2.6×0.45×2 Slotted head screw M2×0.4×8					
UNITS mm		SCALE 2 : 1	COUNT △	DESCRIPTION OF REVISIONS	DESIGNED CHECKED DATE
HRS HIROSE ELECTRIC CO., LTD.		APPROVED : TP. KOMATSU	20230508	DRAWING NO.	EDC-006652-81-00
		CHECKED : HY. KOBAYASHI	20230508	PART NO.	RM15TPD-10P(81)
		DESIGNED : HT. ZENBA	20230508	CODE NO.	CL0109-0601-6-81
		DRAWN : KR. SUZUKI	20230508		