


Sep.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes) 1. This product disassembled when delivered.  
2. Assembly of product to be as figure shown.  
△ 3. Applicable crimp contact : HR10-PC-113(71), applicable wire : AWG#26~#30.  
4. Applicable clamping jig : RP6-SC-TP.  
△ 5. The cable clamping power and the turning force, etc. are different according to the structure of the cable, and use it, please after it confirms it beforehand.  
△ 6 The recommended tightening torque, Ref. No. ⑤ : 0.17 to 0.2 N · m.

3	PBT	(Black) UL94V-0							
2	Zink alloy	Nickel plating	5	Steel	Nickel plating	Tapping screw M2×4			
1	Zink alloy	Nickel plating	4	PVC	(Black) UL94V-0				
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS				
UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00003618		DESIGNED TH. KAMEYA	CHECKED HY. KOBAYASHI	DATE 20191105	
HIROSE ELECTRIC CO., LTD.		APPROVED : TM. AKIYAMA	20051201	DRAWING NO. EDC-047184-71-71					
		CHECKED : TM. AKIYAMA	20051201	PART NO. HR212-10P-10PC(71)					
		DESIGNED : HS. KAWASHIMA	20051119	CODE NO. CL112-4052-4-71					
		DRAWN : HS. KAWASHIMA	20051119						