





Oct.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Reference PCB Layout (Connector Mounting Side) (t = 1.6)




General tolerance is +/- 0.05

Reference Metal Mask Layout (t = 0.15)




General tolerance is +/- 0.02

Mated Condition (Free)



Reference Dimensions of Panel Cutout (Free)



Thickness of metal mask is 0.1 mm min.

Metal mask dimensions of the drawings described, are reference dimensions for 0.15 mm thickness metal mask.

Change the metal mask dimensions by thickness of the metal mask, thickness of PCB, component of solder paste and mounting conditions.

Change the metal mask dimensions in case of mounting IX61G2-*-10P in parallel.

Change the metal mask dimensions, if there are other mounting parts or implementation pattern around the portion of mounting position of IX61G2-*-10P.

Refer to the technical specification (ETAD-E3221-00) for different variations of the metal mask pattern width.

HRS

DRAWING NO.	EDC-388563-00-00
PART NO.	IX61G2-A-10P
CODE NO.	CL0251-0087-0-00

4/2/3

