








- NOTES:
- MATERIALS:
PLASTICS : HIGH TEMPERATURE THERMOPLASTIC UL94-0,COLOR: BLACK
SHELL : STAINLESS STEEL
CONTACT: COPPER ALLOY
 - FINISH
TERMINAL :
CONTACT AREA : SELECTED GOLD PLATING, REFER TO TABLE ON SHEET 2
SOLDER AREA : GOLD FLASH 0.025µm(1µ") MIN.
UNDER PLATING: NICKEL PLATING 1.27µm(50µ") MINIMUM OVERALL.
SHELL :
SOLDERABLE NICKEL PLATING 100µ"(2.54µm")MIN. OVERALL
 - CONNECTOR SHALL BE PACKED IN TAPE AND REEL AS PER PACKAGE SPECIFICATION IN P/N TABLE.
 - CONNECTOR INTENDED TO MATE WITH PLUG CABLE SERIES 215070 AND 215073.
 - RoHS COMPLIANT.
 - DATE CODE LOCATION SHOWN, DATE CODE FORMAT: LDDDYX
L: MOLEX INTERNAL CONTROL
DDD: DAY OF THE YEAR
Y: LAST DIGIT OF THE YEAR
X: MOLEX INTERNAL CONTROL

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
F A = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: Added OOC P/N 21708214**			molex MCIO 4X VERTICAL RECEPTACLE STANDARD TYPE_GEN5						
	MM		8:1											
	GENERAL TOLERANCES (UNLESS SPECIFIED)													
ANGULAR TOL		±		2°										
F E = 0	4 PLACES		±					STATUS: Production DRWN: Serway Yang CHK'D: Samuel Hou APPR: Rex Tsai			PRODUCT CUSTOMER DRAWING			
	3 PLACES		± 0.1000											
	2 PLACES		± 0.200											
	1 PLACE		± 0.30											
	0 PLACES		±											
F P = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION	
					C-SIZE		217082		2170821011		PSD	000	C	
									2024-09-04 2024-10-04 2024-10-04					
DIVISIONAL SYMBOLS									MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
											GENERAL MARKET		1 OF 5	

