








1. GENERAL:
 - 1.1 PRODUCT SPECIFICATION: 2204090000-PS
 - 1.2 TEST SUMMARY: 2050001000-TS
 - 1.3 APPLICATION SPECIFICATION: 2204090000-AS
 - 1.4 PACKAGING SPECIFICATION: 2050001000-PK
 - 1.5 COSMETIC SPECIFICATION: PS-45499-002 CLASS B
 - 1.6 SOLDERABILITY SPECIFICATION: SMES-152
 - 1.7 MATES WITH: 20431411XX
 - 1.8 PART MOUNTED WITH CONDUCTIVE M3X1.0 SCREW AND CONDUCTIVE BELLEVILLE WASHER FOR OPTIMAL PERFORMANCE.
1.8 +/- .1Nm TORQUE
2. DESIGN - MATERIALS:
 - 2.1 CONTACT MATERIAL: COPPER ALLOY
 - 2.2 RETENTION CAP : STAINLESS STEEL
 - 2.3 PLATING:
 - i CONTACT AREA: GOLD.
 - ii. REST AREA: SILVER WITH TARNISH INHIBITOR
 - iii CAGE : 1.5 MICRON MIN TIN OVER 1.27 MICRON MIN NICKEL



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex											
mm																			
GENERAL TOLERANCES (UNLESS SPECIFIED)																			
ANGULAR TOL ± 1.0 °																			
4 PLACES		±																	
3 PLACES		±		EC NO: 811790 DRWN: JAYK1 2025/02/05 CHK'D: BPISZCZOR 2025/02/25 APPR: BPISZCZOR 2025/02/25				3.4MM SENTRALITY RA SCREW ASM W/FLOAT											
2 PLACES		± 0.15																	
1 PLACE		± 0.2																	
0 PLACES		±		INITIAL REVISION: DRWN: JAYK1 2023/09/13 APPR: BPISZCZOR 2024/01/23				PRODUCT CUSTOMER DRAWING											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
								 		D-SIZE		205000						1 OF 1	