




SIZE	'A' +0.03 -0.13	'B' TYP.	'C' MAX.	'D' ±0.13	'E' ±0.41	'L' +0.79 -0
08	12.01	15.09	21.03	3.05	1.57	11.73
10	14.99	18.26	24.23			
12	19.05	20.62	26.59			
14	22.22	23.01	28.98			
16	25.40	24.61	31.34			
18	28.57	26.97	33.73			
20	31.75	29.36	36.91	3.73	2.39	14.12
22	34.92	31.75	40.08			
24	38.10	34.93	43.26			14.96

MILITARY PART NO. INFORMATION

JANMS3115-12W

Series

Finish

Shell Size

8,10,12,14,16,18,20,22,24

A - Hard Anodize black finish.
K - Black Zinc Nickel Finish.
L - Electroless Nickel Plate Finish.
W - Cadmium Olive Drab Finish.

PROPRIETARY PART NO. INFORMATION

62IN-3115-10-XXX

Series

Dummy shell.

Finish

Shell size

08,10,12,14,16,18,20,22,24

(416) Electroless nickel finish.
(610) Hard anodize black.
(622) Cad. free zinc cobalt-Olive drab finish.
(624) Cad. free zinc cobalt-Black finish.
(714) Cadmium Olive Drab Finish.
(626) Black Zinc Nickel Finish.

Material:-

1. R/SHELL - ALUMINIUM ALLOY
2. GASKET - SILICONE RUBBER (RED)
3. BAYONET STUD- STAINLESS STEEL ALLOY.

4	27/07/17
3	25/05/15
2	16/2/13
1	20/8/09
Issue No.	Rev. Date.

ALL DIM'S ARE IN MM

DUMMY RECEPT. SHELL ASSY. FOR MIL-DTL-26482 CONNECTORS, SERIES 1 AND 2				Amphenol Amphenol Interconnect India Pvt. Ltd. PUNE-411026	
Scale 3:1	Dwg. No. C-80131/6	Drawn by. Kulkarni	Date 20/8/09		