

18 AND 23 GHz 2 WATTS

Electrical:

Standard Freq. Values _____ 18 & 23 GHz

Attenuation Accuracy:	DC-18 GHz	18-23 GHz
1dB	±0.3 dB	±0.5 dB
0, and 2 - 6 dB	±0.3 dB	±0.4 dB
7 - 20 dB	±0.5 dB	±0.6 dB
21 - 30 dB	±0.75 dB	±0.8 dB

VSWR:

DC - 4 GHz _____ 1.15:1 Max.

8 - 12.4 GHz _____ 1.25:1 Max.

18 - 23 GHz _____ 1.40:1 Max.

DERATED LINEARLY TO 0.5 WATTS @ +125°C

(5uSec Pulse, .05% Duty Cycle)

Operating Temp Range _____ -65°C to +125°C

Mechanical:

Conductors _____ Gold Plated Beryllium Copper



MALE/MALE AND FEMALE/FEMALE CONFIGURATIONS NOT SHOWN

FORMAT: IN-TC-Ed-prod-C
CD-450241-0

</

[illegible]