

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	INITIAL RELEASE	MAR13/24	K.T

- NOTES:**
ELECTRICAL:
 1. VOLTAGE RATING: 125 VAC.
 2. CURRENT RATING: 1.25 AMPS PER CONTACT.
 3. INSULATING RESISTANCE: 500 MEGAOHMS MINIMUM.
 4. DIELECTRIC STRENGTH: 1000 VAC 60Hz, 1MIN.
 5. CATEGORY 5e CHARACTERISTIC

FREQUENCY MHZ	NEAR-END CROSSTALK dB, MIN.	RETURN LOSS dB , MIN.	INSERTION LOSS dB, MAX.
1.0	65.0	30.0	0.1
4.0	65.0	30.0	0.1
8.0	64.9	30.0	0.1
10.0	63.0	30.0	0.1
16.0	58.9	30.0	0.2
20.0	57.0	30.0	0.2
25.0	55.0	30.0	0.2
31.25	53.1	30.0	0.2
62.5	47.1	24.1	0.3
100.0	43.0	20.0	0.4







- MECHANICAL:**
 1. SHIELD: STAINLESS STEEL WITH TIN-DIP ON SOLDER TABS
 2. HOUSING: THERMOPLASTIC, UL 94V-0, BLACK
 3. CONTACT: PHOSPHOR BRONZE,
 SELECTIVE GOLD PLATING ON MATING SURFACE,
 50µ" MIN. NICKEL UNDERPLATE
 100µ" MATTE TIN PLATING ON CONTACT SOLDER TAIL.

- ENVIRONMENTAL:**
 1. STORAGE : -40 °C TO +85°C
 2. OPERATION:-40 °C TO +85°C
 3. MATES WITH MODULAR PLUG CONFORMING TO TIA 1096 STANDARD.
 4. RECOMMENDED SOLDER PROCESS:
 WAVE SOLDER, PEAK TEMPERATURE 260°C FOR 5-8 SECONDS

RJ CONNECTOR CONFORMS TIA-1096

AMPHENOL PART NUMBER DESCRIPTION: RJE58-488-6X01

GOLD PLATING OPTION
 1=6µ" GOLD PLATING
 2=15µ" MIN GOLD PLATING
 3=30µ" MIN GOLD PLATING
 4=50µ" MIN GOLD PLATING





**RECOMMENDED PCB LAYOUT
 TOLERANCE: ±0.05[0.002]**



UNLESS SPECIFIED OTHERWISE	DRAWN	J.CHEN	MAR13/24
PRIMARY UNITS MILLIMETERS	CHECKED	K.TANG	MAR13/24
SECONDARY INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.		
1 DECIMAL PLACE	ENG. REL. NO.	EAR 15463	
2 DECIMAL PLACES ±0.25	REF.		
3 DECIMAL PLACES ±0.15	THIRD ANGLE PROJECTION		
ANGULAR DEGREES ±2°			

Amphenol Canada Corp. Commercial Products			
MODULAR JACK, 1X4 PORTS, 8 POSITIONS, 8 CONTACTS, SHIELDED WITHOUT TABS, WITHOUT LEDS, TAB UP, CAT 5e, RoHS COMPLIANT			
DWG. NO.	P-RJE58-488-6X01		
CODE ID NO. 03554	DWG. SIZE: N/A	SCALE: FIT	SHEET 1 OF 2

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	INITIAL RELEASE	MAR13/24	K.T



RECOMMENDED PANEL CUTOUT

TRAY PACKING INFORMATION		
CONNECTORS PER TRAY	TRAYS PER CARTON	TOTAL CONNECTORS PER CARTON
20PCS	22PCS	440PCS



UNLESS SPECIFIED OTHERWISE	DRAWN	J.CHEN	MAR13/24
PRIMARY UNITS MILLIMETERS	CHECKED	K.TANG	MAR13/24
SECONDARY INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.		
1 DECIMAL PLACE	ENG. REL. NO.	EAR 15463	
2 DECIMAL PLACES ±0.25	REF.		
3 DECIMAL PLACES ±0.15	THIRD ANGLE PROJECTION		
ANGULAR DEGREES ±2°			

Amphenol Canada Corp. Commercial Products			
MODULAR JACK, 1X4 PORTS, 8 POSITIONS, 8 CONTACTS, SHIELDED WITHOUT TABS, WITHOUT LEDS, TAB UP, CAT 5e, RoHS COMPLIANT			
DWG. NO. P-RJE58-488-6X01			REV A
CODE ID NO. 03554	DWG SIZE: N/A	SCALE: FIT	SHEET 2 OF 2