
NOTICE OF PROPRIETARY RIGHTS
THIS DOCUMENT CONTAINS CONFIDENTIAL TECHNICAL DATA, INCLUDING TRADE SECRETS, PROPRIETARY TO TIMES MICROWAVE SYSTEMS. DISCLOSURE OF THIS DATA IS EXPRESSLY CONDITIONED UPON YOUR ASSENT THAT ITS USE IS LIMITED TO USE WITHIN YOUR COMPANY ONLY. ANY OTHER USE IS STRICTLY PROHIBITED WITHOUT THE PRIOR WRITTEN CONSENT OF TIMES MICROWAVE SYSTEMS.

MYZ	REVISION DESCRIPTION	DFTM	DATE	APPD	DATE
\supset	RELEASED FOR PRODUCTION	n.n.n	3/26/14	J.D.B.	4/1/14



BODY	CONTACT
ALBALOY	GOLD/NI

3.0 FINISHES: SEE TABLE

4.0 MECHANICAL

1.0 PERFORMANCE

1.1 FREQUENCY RANGE: DC-6 GHz

1.2 NOMINAL IMPEDANCE: 50 OHMS

1.3 DWV: 750 VRMS @ 60 Hz (SEA LEVEL)

1.4 TEMPERATURE RANGE: -65°C TO +165°C 2.4 CRIMP FERRULE: SOFT COPPER

2.0 MATERIALS

2.1 DIELECTRIC: PTFE

2.2 CONTACT: BERYLLIUM COPPER

2.3 LOCKING RING: PHOSPHOR BRONZE 4.1 INTERFACE REF MIL-STD-348

2.5 OTHER METAL PARTS: BRASS

2.6 GASKET: SILICONE RUBBER

2.7 HEAT SHRINK: POLYOLEFIN THICK WALL

DFTM.N.N.N MATL: UNLESS OTHERWISE SPECIFIED TIMES MICROWAVE SYSTEMS ALL DIMENSIONS ARE IN INCHES DATE 3/26/14 MACHINED SURFACES FINISHN/A RMS MAX. REMOVE ALL BURRS . 005 MAX. BREAK CHKD. J. D. B EZ-240-TM-RP-X MACHINE CURNERS . 005 MAX. FILLET R.
TULERANCES UN DECIMALS
. XX ± . 03 . XXX ± . 005 DATE 4/1/14 USED ON: B RP TNCM APPD. J. D. B. FOR LMR-240 CABLE ANGLES ± 1° FRACTIONS ± 1/32 SD3190-2892 DO NOT SCALE DRAWING CODE 68999 DATE 4/1/14 SCALE: N/A