





8 7 6 5 4 3 2 1

NOTICE OF PROPRIETARY RIGHTS: THIS DOCUMENT CONTAINS CONFIDENTIAL DATA, INCLUDING TRADE SECRETS, PROPRIETARY TO TIMES MICROWAVE SYSTEMS. DISCLOSURE OF THIS DATA IS EXPRESSLY CONDITIONED UPON YOUR ASSENT THAT ITS USE IS LIMITED TO USE WITHIN YOUR COMPANY ONLY. ANY OTHER USE IS STRICTLY PROHIBITED WITHOUT THE PRIOR WRITTEN CONSENT OF TIMES MICROWAVE SYSTEMS.

VER	Description	ECN	Name	Date
A	Initial Released	N/A	Patrick	2018/09/30



RECOMMENDED MOUNTING HOLE



RECOMMENDED CABLE STRIPPING DIM'S
Connector Adds: 32.8 mm

Compatible with Standard: IEC 60169-17

UNLESS OTHERWISE SPECIFIED				DFTM Patrick		 An Amphenol Company			
ALL DIMENSIONS ARE IN mm MACHINED SURFACES FINISH 1.6 RMS MAX. REMOVE ALL BURRS 0.15X45° MAX. BREAK MACHINE CORNERS 0.15X45° D MAX. FILLET R. TOLERANCES ON DECIMALS X ±0.1 .XX ±0.15 ANGLES ±2° FRACTIONS ± N/A				DATE	2018/09/30				
				CHKD	Monica	EZ-400-TF-BH-X			
				DATE	2018/09/30	TNC Female (Jack) Straight Non-Solder Pin No Braid Trim Bulkhead Connector for LMR-400 Cable			
				APPD	Joslen				
Scale:	3:1	Size:	A3	CODE IDENT	68999	DATE	2018/09/30	SHT	1/1
								3190-8024	REV A