

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

23




© COPYRIGHT 23

BY -



ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	02FEB2024	F.Z	R.B




CIRCUIT NUMBER



- 1 MATERIAL
HOUSING: THERMO PLASTICS BLACK
CONTACT: COPPER ALLOY
SPRING: STAINLESS
2 PLATING
0.002mmMIN NICKEL PLATING OVER ALL
CONTACT POINT: UNDER Ni PLATING
0.0002mmMIN OVER Au PLATING.
WIRE CLAMPING POINT: UNDER Ni PLATING
0.002mmMIN OVER Tin PLATING.

1-2475345-2(6極 キーイングY) BLACK

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER.ZHU 11OCT2023	 TE Connectivity				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.3	CHK RICK.BIAN 13OCT2023					
		APVD RICK.BIAN 13OCT2023					
		PRODUCT SPEC 108-161106	NAME DYNAMIC D3950 RECEPTACLE ASSEMBLY -				
MATERIAL 		APPLICATION SPEC 411-78272					
FINISH 		WEIGHT -	SIZE A3	CAGE CODE -	DRAWING NO C-2475345	RESTRICTED TO -	
CUSTOMER DRAWING					SCALE 2:1	SHEET 1 OF 1	REV A