

HOW TO REQUEST NEW PLATE CONFIGURATIONS
(SEE PART NUMBER TABLE FOR CURRENT RELEASED PLATES)
STANDARD (SHEET 2) OR HIGH DENSITY (SHEET 3) SPACING
RoHS YES (SILVER PLATING)/NO (TIN PLATING)
NUMBER OF ROWS
NUMBER OF LINES PER ROW (PLATE SIZE RESTRICTED, SEE SHEETS 2+3)
FILTER DESIGNATION (SEE FILTER DESIGNATION TABLE)
PLATE LENGTH (SEE TABLES ON SHEETS 2 + 3)
LEAD CONFIGURATION PER SHEETS 2 + 3: STRAIGHT (0), LEFT (1), RIGHT (2), BOTH (3)
SELECTIVE LINE FILTERING ALSO AVAILABLE, CONTACT MOLEX FOR CUSTOM CONFIGURATIONS


FILTER DESIGNATION SELECTION TABLE

Filter Designation	Filter*** Circuits	Capacitance		3 dB Max Cut-of Frequency (MHz)	Working Voltage DC -55°C to +125°C	Minimum Insertion Loss - Decibels (dB) 50ohm system per MIL-STD-220 (no load)							
		Value	Tolerance			5 MHZ	10 MHZ	20 MHZ	50 MHZ	100 MHZ	200 MHZ	500 MHZ	1 GHZ
A	C	68pF	+/-25%	73.9	100V	-	-	-	-	-	3	10	16
B	C	100pF	+/-25%	50.3	100V	-	-	-	-	1	6	13	19
C	C	135pF	+100/-0%	23.3	100V	-	-	-	1	5	10	16	20
D	C	470pF	+/-25%	10.7	100V	-	-	2	7	13	18	25	27
E	C	820pF	+/-25%	6.2	100V	-	1	5	12	18	23	30	33
F	C	1000pF	+/-25%	5.1	100V	-	2	7	14	20	25	32	35
G	C	1500pF	+/-25%	3.4	100V	1	4	10	16	22	29	36	37
H	C	2500pF	+100/-0%	1.26	100V	5	11	17	23	29	35	38	40
I	C	4000pF	+100/-0%	0.8	100V	9	15	21	27	34	38	42	46
J	Insulated	10pF	Max.	635	100V	-	-	-	-	-	-	-	-
K	Grounded					-	-	-	-	-	-	-	-
L	Pi	68	+/-25%	65.3	100V	-	-	-	-	1	3	8	19
M	Pi	100	+/-25%	45.1	100V	-	-	-	-	2	6	11	27
N	Pi	135	+100/-0%	22.0	100V	-	-	-	1	6	10	20	34
O	Pi	470	+/-25%	10.6	100V	-	-	-	8	14	21	36	43
P	Pi	820	+/-25%	6.2	100V	-	-	4	13	22	31	45	52
Q	Pi	1000	+/-25%	5.1	100V	-	2	6	14	22	33	51	59
R	Pi	1700	+100/-0%	1.9	100V	1	6	12	23	35	48	64	69
S	Pi	2500	+100/-0%	1.3	50V	4	9	15	28	41	54	70	70
T	Pi	5000	+100/-0%	0.65	100V	9	15	23	41	53	66	70	70

*** FOR HIGH DENSITY FILTER PLATES (2mm CENTERS) ONLY C STYLE FILTERS ARE AVAILABLE

NOTES:

1. MATERIALS:
 - PLATE: BRASS PER UNS C26000/C27000
 - LEADS: COPPER ALLOY
2. PLATING:
 - PLATE:
 - RoHS COMPLIANT: SILVER
 - NON-RoHS COMPLIANT: MATTE TIN
 - LEADS: GOLD
3. PLATES MARKED WITH: MOLEX. MOLEX P/N AND DATE CODE IN YYWW FORMAT








FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
F_A = 0 F_E = 0 F_B = 0 DIVISIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC: RELEASED							
		INCH/mm		NTS									
		GENERAL TOLERANCES (UNLESS SPECIFIED)											
			MM	INCH									
		4 PLACES		±	±								
		3 PLACES		±	±								
		2 PLACES		±	±								
		1 PLACE		±	±								
		0 PLACES		±	±								
ANGULAR TOL		±	0.5°		STATUS: Production DRWN: Kevin Tagan 2024-08-20 CHK'D: Les Meier 2024-08-20 APPR: James Borrelli 2024-08-20								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													
THIRD ANGLE PROJECTION													
				DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				C-SIZE		73286		SEE TABLE		GENERAL MARKET		1 OF 4	

STANDARD DENSITY
.100 [2.54] CENTERS
LEAD DIAMETER = .025 [0.64]
CURRENT RATING: 5 AMPS

Plate length (A)	No. of filtered lines per row	STANDARD DENSITY	
		B	C
1.060* (26.92)	1	0 (0.00)	0.53 (13.46)
	2	0.1 (2.54)	0.43 (10.92)
	3	0.2 (5.08)	0.43 (10.92)
	4	0.3 (7.62)	0.33 (8.38)
	5	0.4 (10.16)	0.33 (8.38)
1.560* (39.62)	1	0 (0.00)	0.73 (18.54)
	2	0.1 (2.54)	0.73 (18.54)
	3	0.2 (5.08)	0.63 (16.00)
	4	0.3 (7.62)	0.63 (16.00)
	5	0.4 (10.16)	0.53 (13.46)
	6	0.5 (12.70)	0.53 (13.46)
	7	0.6 (15.24)	0.43 (10.92)
	8	0.7 (17.78)	0.43 (10.92)
	9	0.8 (20.32)	0.33 (8.38)
	10	0.9 (22.86)	0.33 (8.38)
2.560 (65.02)	5	0.4 (10.16)	1.03 (26.16)
	6	0.5 (12.70)	1.03 (26.16)
	7	0.6 (15.24)	0.93 (23.62)
	8	0.7 (17.78)	0.93 (23.62)
	9	0.8 (20.32)	0.83 (21.08)
	10	0.9 (22.86)	0.83 (21.08)
	11	1.0 (25.40)	0.73 (18.54)
	12	1.1 (27.94)	0.73 (18.54)
	13	1.2 (30.48)	0.63 (16.00)
	14	1.3 (33.02)	0.63 (16.00)
	15	1.4 (35.56)	0.53 (13.46)
	16	1.5 (38.10)	0.53 (13.46)
	17	1.6 (40.65)	0.43 (10.92)
	18	1.7 (43.18)	0.43 (10.92)
	19	1.8 (45.72)	0.33 (8.38)
3.560 (90.42)	20	1.9 (48.26)	0.33 (8.38)
	13	1.2 (30.48)	1.13 (27.70)
	14	1.3 (33.02)	1.13 (27.70)
	15	1.4 (35.56)	1.03 (26.16)
	16	1.5 (38.10)	1.03 (26.16)
	17	1.6 (40.65)	0.93 (23.62)
	18	1.7 (43.18)	0.93 (23.62)
	19	1.8 (45.72)	0.83 (21.08)
	20	1.9 (48.26)	0.83 (21.08)
	21	2.0 (50.80)	0.73 (18.54)
	22	2.1 (53.34)	0.73 (18.54)
	23	2.2 (55.88)	0.63 (16.00)
	24	2.3 (55.42)	0.63 (16.00)
	25	2.4 (60.96)	0.53 (13.46)
	26	2.5 (63.50)	0.53 (13.46)
	27	2.6 (66.04)	0.43 (10.92)
	28	2.7 (68.58)	0.43 (10.92)
	29	2.8 (71.12)	0.33 (8.38)
	30	2.9 (73.66)	0.33 (8.38)

* 1.060 (26.92) AND 1.560 (39.62) LONG PLATES DO NOT HAVE COINING. INCREASE THESE DIMENSIONS BY .020 (0.51) IF USING THESE SIZED PLATES
** DIMENSION NOT APPLICAPIBLE FOR SINGLE ROW DESIGNS








FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
	DIMENSION UNITS		SCALE		CURRENT REV DESC: RELEASED														
	INCH/mm		NTS																
	GENERAL TOLERANCES (UNLESS SPECIFIED)																		
		MM	INCH																
	$\frac{F}{A} = 0$					molex BOLT-IN FILTER PLATES PRODUCT CUSTOMER DRAWING <table><tr><td>DOCUMENT NUMBER</td><td>DOC TYPE</td><td>DOC PART</td><td>REVISION</td></tr><tr><td>732860010</td><td>PSD</td><td>000</td><td>A</td></tr></table>						DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION	732860010	PSD	000	A
	DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION															
	732860010	PSD	000	A															
	$\frac{F}{C} = 0$																		
	$\frac{F}{P} = 0$																		
DIVISIONAL SYMBOLS				STATUS: Production															
				DRWN: Kevin Tagan 2024-08-20															
				CHK'D: Les Meier 2024-08-20															
				APPR: James Borrelli 2024-08-20															
				ANGULAR TOL ± 0.5°															
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS															
				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER					
						C-SIZE		73286		SEE TABLE		GENERAL MARKET		2 OF 4					

HIGH DENSITY
.079 [2.00] CENTERS
LEAD DIAMETER = .020 [0.51]
CURRENT RATING: 3 AMPS

Plate length (A)	No. of filtered lines per row	HIGH DENSITY	
		B	C
1.060* (26.92)	2	0.079 (2.00)	0.487 (12.38)
	3	0.157 (4.00)	0.409 (10.38)
	4	0.236 (6.00)	0.409 (10.38)
	5	0.315 (8.00)	0.330 (8.38)
	6	0.394 (10.00)	0.330 (8.38)
1.560* (39.62)	3	0.157 (4.00)	0.662 (16.81)
	4	0.236 (6.00)	0.662 (16.81)
	5	0.315 (8.00)	0.583 (14.81)
	6	0.394 (10.00)	0.583 (14.81)
	7	0.472 (12.00)	0.504 (12.81)
	8	0.551 (14.00)	0.504 (12.81)
	9	0.630 (16.00)	0.426 (10.81)
	10	0.709 (18.00)	0.426 (10.81)
	11	0.787 (20.00)	0.347 (8.81)
	12	0.866 (22.00)	0.347 (8.81)
	10	0.709 (18.00)	0.886 (22.51)
	11	0.787 (20.00)	0.886 (22.51)
2.560 (65.02)	12	0.866 (22.00)	0.807 (20.51)
	13	0.945 (24.00)	0.807 (20.51)
	14	1.024 (26.00)	0.729 (18.51)
	15	1.102 (28.00)	0.729 (18.51)
	16	1.181 (30.00)	0.650 (16.51)
	17	1.260 (32.00)	0.650 (16.51)
	18	1.339 (34.00)	0.571 (14.51)
	19	1.417 (36.00)	0.571 (14.51)
	20	1.496 (38.00)	0.492 (12.51)
	21	1.575 (40.00)	0.492 (12.51)
	22	1.654 (42.00)	0.414 (10.51)
	23	1.732 (44.00)	0.414 (10.51)
	24	1.811 (46.00)	0.335 (8.51)
	25	1.890 (48.00)	0.335 (8.51)
	20	1.496 (38.00)	0.993 (25.22)
	21	1.575 (40.00)	0.993 (25.22)
	22	1.654 (42.00)	0.914 (23.22)
	23	1.732 (44.00)	0.914 (23.22)
3.560 (90.42)	24	1.811 (46.00)	0.835 (21.22)
	25	1.890 (48.00)	0.835 (21.22)
	26	1.969 (50.00)	0.757 (19.22)
	27	2.047 (52.00)	0.757 (19.22)
	28	2.126 (54.00)	0.678 (17.22)
	29	2.205 (56.00)	0.678 (17.22)
	30	2.283 (58.00)	0.599 (15.22)
	31	2.362 (60.00)	0.599 (15.22)
	32	2.441 (62.00)	0.520 (13.22)
	33	2.520 (64.00)	0.520 (13.22)
	34	2.598 (66.00)	0.442 (11.22)
	35	2.677(68.00)	0.442 (11.22)
	36	2.756 (70.00)	0.363 (9.22)
	37	2.835(72.00)	0.363 (9.22)

* 1.060 (26.92) AND 1.560 (39.62) LONG PLATES DO NOT HAVE COINING. INCREASE THESE DIMENSIONS BY .020 (0.51) IF USING THESE SIZED PLATES
** DIMENSION NOT APPLICAIABLE FOR SINGLE ROW DESIGNS



FUNCTIONAL SYMBOLS

$\frac{F}{A} = 0$

$\frac{F}{E} = 0$

$\frac{F}{D} = 0$

DIVISIONAL SYMBOLS

DIMENSION UNITS

INCH/mm

SCALE

NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	±
2 PLACES	±	±
1 PLACE	±	±
0 PLACES	±	±

ANGULAR TOL ± 0.5°

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

CURRENT REV DESC: RELEASED

STATUS: Production

DRWN: Kevin Tagan

CHK'D: Les Meier

APPR: James Borrelli

2024-08-20

2024-08-20

2024-08-20

THIRD ANGLE PROJECTION

DRAWING

C-SIZE

SERIES 73286

DOCUMENT NUMBER

732860010

DOC TYPE

PSD

DOC PART

000

REVISION

A

PRODUCT CUSTOMER DRAWING

MATERIAL NUMBER

SEE TABLE

CUSTOMER

GENERAL MARKET

SHEET NUMBER

3 OF 4

molex

BOLT-IN FILTER PLATES

FORMAT: INTCG-prod-01

REVISION: 0

DATE: 20230501

12

11

10

9

8

7

6

5

4

3

2

1

HOW TO REQUEST NEW PLATE CONFIGURATIONS
(SEE PART NUMBER TABLE FOR CURRENT RELEASED PLATES)
STANDARD (SHEET 2) OR HIGH DENSITY (SHEET 3) SPACING
RoHS YES (SILVER PLATING)/NO (TIN PLATING)
NUMBER OF ROWS
NUMBER OF LINES PER ROW (PLATE SIZE RESTRICTED, SEE SHEETS 2+3)
FILTER DESIGNATION (SEE FILTER DESIGNATION TABLE)
PLATE LENGTH (SEE TABLES ON SHEETS 2 + 3)
LEAD CONFIGURATION PER SHEETS 2 + 3: STRAIGHT (0), LEFT (1), RIGHT (2), BOTH (3)
SELECTIVE LINE FILTERING ALSO AVAILABLE, CONTACT MOLEX FOR CUSTOM CONFIGURATIONS


FILTER DESIGNATION SELECTION TABLE

Filter Designation	Filter*** Circuits	Capacitance		3 dB Max Cut-of Frequency (MHz)	Working Voltage DC -55°C to +125°C	Minimum Insertion Loss - Decibels (dB) 50ohm system per MIL-STD-220 (no load)							
		Value	Tolerance			5 MHZ	10 MHZ	20 MHZ	50 MHZ	100 MHZ	200 MHZ	500 MHZ	1 GHZ
A	C	68pF	+/-25%	73.9	100V	-	-	-	-	-	3	10	16
B	C	100pF	+/-25%	50.3	100V	-	-	-	-	1	6	13	19
C	C	135pF	+100/-0%	23.3	100V	-	-	-	1	5	10	16	20
D	C	470pF	+/-25%	10.7	100V	-	-	2	7	13	18	25	27
E	C	820pF	+/-25%	6.2	100V	-	1	5	12	18	23	30	33
F	C	1000pF	+/-25%	5.1	100V	-	2	7	14	20	25	32	35
G	C	1500pF	+/-25%	3.4	100V	1	4	10	16	22	29	36	37
H	C	2500pF	+100/-0%	1.26	100V	5	11	17	23	29	35	38	40
I	C	4000pF	+100/-0%	0.8	100V	9	15	21	27	34	38	42	46
J	Insulated	10pF	Max.	635	100V	-	-	-	-	-	-	-	-
K	Grounded					-	-	-	-	-	-	-	-
L	Pi	68	+/-25%	65.3	100V	-	-	-	-	1	3	8	19
M	Pi	100	+/-25%	45.1	100V	-	-	-	-	2	6	11	27
N	Pi	135	+100/-0%	22.0	100V	-	-	-	1	6	10	20	34
O	Pi	470	+/-25%	10.6	100V	-	-	-	8	14	21	36	43
P	Pi	820	+/-25%	6.2	100V	-	-	4	13	22	31	45	52
Q	Pi	1000	+/-25%	5.1	100V	-	2	6	14	22	33	51	59
R	Pi	1700	+100/-0%	1.9	100V	1	6	12	23	35	48	64	69
S	Pi	2500	+100/-0%	1.3	50V	4	9	15	28	41	54	70	70
T	Pi	5000	+100/-0%	0.65	100V	9	15	23	41	53	66	70	70

*** FOR HIGH DENSITY FILTER PLATES (2mm CENTERS) ONLY C STYLE FILTERS ARE AVAILABLE

NOTES:

1. MATERIALS:
 - PLATE: BRASS PER UNS C26000/C27000
 - LEADS: COPPER ALLOY
2. PLATING:
 - PLATE:
 - RoHS COMPLIANT: SILVER
 - NON-RoHS COMPLIANT: MATTE TIN
 - LEADS: GOLD
3. PLATES MARKED WITH: MOLEX. MOLEX P/N AND DATE CODE IN YYWW FORMAT









FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
		DIMENSION UNITS		SCALE		CURRENT REV DESC: RELEASED													
DIVISIONAL SYMBOLS		INCH/mm		NTS								molex BOLT-IN FILTER PLATES PRODUCT CUSTOMER DRAWING <table><tr><td>DOCUMENT NUMBER</td><td>DOC TYPE</td><td>DOC PART</td><td>REVISION</td></tr><tr><td>732870010</td><td>PSD</td><td>000</td><td>A</td></tr></table>						DOCUMENT NUMBER	DOC TYPE
		DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION														
		732870010	PSD	000	A														
		GENERAL TOLERANCES (UNLESS SPECIFIED)																	
			MM	INCH															
		4 PLACES	±	±															
		3 PLACES	±	±															
		2 PLACES	±	±															
1 PLACE	±	±																	
0 PLACES	±	±																	
ANGULAR TOL ± 0.5°				STATUS: Production DRWN: Kevin Tagan 2024-08-14 CHK'D: Les Meier 2024-08-19 APPR: James Borrelli 2024-08-19															
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																			
		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER							
				C-SIZE		73287		SEE TABLE		GENERAL MARKET		1 OF 4							

STANDARD DENSITY
.100 [2.54] CENTERS
LEAD DIAMETER = .025 [0.64]
CURRENT RATING: 5 AMPS

Plate length (A)	No. of filtered lines per row	STANDARD DENSITY	
		B	C
1.060* (26.92)	1	0 (0.00)	0.53 (13.46)
	2	0.1 (2.54)	0.43 (10.92)
	3	0.2 (5.08)	0.43 (10.92)
	4	0.3 (7.62)	0.33 (8.38)
	5	0.4 (10.16)	0.33 (8.38)
1.560* (39.62)	1	0 (0.00)	0.73 (18.54)
	2	0.1 (2.54)	0.73 (18.54)
	3	0.2 (5.08)	0.63 (16.00)
	4	0.3 (7.62)	0.63 (16.00)
	5	0.4 (10.16)	0.53 (13.46)
	6	0.5 (12.70)	0.53 (13.46)
	7	0.6 (15.24)	0.43 (10.92)
	8	0.7 (17.78)	0.43 (10.92)
	9	0.8 (20.32)	0.33 (8.38)
	10	0.9 (22.86)	0.33 (8.38)
2.560 (65.02)	5	0.4 (10.16)	1.03 (26.16)
	6	0.5 (12.70)	1.03 (26.16)
	7	0.6 (15.24)	0.93 (23.62)
	8	0.7 (17.78)	0.93 (23.62)
	9	0.8 (20.32)	0.83 (21.08)
	10	0.9 (22.86)	0.83 (21.08)
	11	1.0 (25.40)	0.73 (18.54)
	12	1.1 (27.94)	0.73 (18.54)
	13	1.2 (30.48)	0.63 (16.00)
	14	1.3 (33.02)	0.63 (16.00)
	15	1.4 (35.56)	0.53 (13.46)
	16	1.5 (38.10)	0.53 (13.46)
	17	1.6 (40.65)	0.43 (10.92)
	18	1.7 (43.18)	0.43 (10.92)
	19	1.8 (45.72)	0.33 (8.38)
3.560 (90.42)	20	1.9 (48.26)	0.33 (8.38)
	13	1.2 (30.48)	1.13 (27.70)
	14	1.3 (33.02)	1.13 (27.70)
	15	1.4 (35.56)	1.03 (26.16)
	16	1.5 (38.10)	1.03 (26.16)
	17	1.6 (40.65)	0.93 (23.62)
	18	1.7 (43.18)	0.93 (23.62)
	19	1.8 (45.72)	0.83 (21.08)
	20	1.9 (48.26)	0.83 (21.08)
	21	2.0 (50.80)	0.73 (18.54)
	22	2.1 (53.34)	0.73 (18.54)
	23	2.2 (55.88)	0.63 (16.00)
	24	2.3 (55.42)	0.63 (16.00)
	25	2.4 (60.96)	0.53 (13.46)
	26	2.5 (63.50)	0.53 (13.46)
	27	2.6 (66.04)	0.43 (10.92)
	28	2.7 (68.58)	0.43 (10.92)
	29	2.8 (71.12)	0.33 (8.38)
	30	2.9 (73.66)	0.33 (8.38)

* 1.060 (26.92) AND 1.560 (39.62) LONG PLATES DO NOT HAVE COINING. INCREASE THESE DIMENSIONS BY .020 (0.51) IF USING THESE SIZED PLATES
** DIMENSION NOT APPLICAIABLE FOR SINGLE ROW DESIGNS



FUNCTIONAL SYMBOLS F_A = 0 F_C = 0 F_P = 0 DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
	DIMENSION UNITS		SCALE		CURRENT REV DESC: RELEASED						molex						
	INCH/mm		NTS														
	GENERAL TOLERANCES (UNLESS SPECIFIED)																
		MM	INCH								BOLT-IN FILTER PLATES						
	4 PLACES	±	±														
	3 PLACES	±	±														
	2 PLACES	±	±														
	1 PLACE	±	±														
	0 PLACES	±	±								PRODUCT CUSTOMER DRAWING						
	ANGULAR TOL		± 0.5°														
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION
						C-SIZE		73287		732870010		PSD		000		A	
										MATERIAL NUMBER		CUSTOMER				SHEET NUMBER	
										SEE TABLE		GENERAL MARKET				2 OF 4	

