



ISS.	AMEND	DATE
1	ISSUED	12/02/15
2	ADD WHITE VARIANTS	26/11/19
3	ADD MIN MAX TEMP	30/06/20
4	MATERIAL PC or ABS	01/03/21
5	UPDATE MATERIALS	04/04/22




Material:

1. RJ45 In-Line Coupler: ABS UL94-V0 Fully Shielded
2. RJ45 In-Line Coupler Contact: Phosphor Bronze, 3-50 micro inches gold plating over nickel plate.
3. PCB: FR4
4. Frame: Polyamide UL94-V2




Performance:

1. T568A & T568B wiring.
2. Meet ISO/IEC 11801 and EN50173
3. Meet ANSI/TIA/EIA 568B.2
4. Rating: 125VAC RMS 1.5A
3. Operating Temperatures: Min -10°C Max +70°C

PART NO.	COLOUR	FIXING HOLE DETAILS
CP30222S	BLACK	HOLE Ø3.5 x CSK 82° x Ø5.85
CP30222SW	WHITE	
CP30222SX	BLACK	PLAIN HOLE Ø2.50
CP30222SXW	WHITE	



FIXING HOLE VARIANTS:
Ø3.5mm CSK 82° x Ø5.85
'X' VERSION HAS Ø2.5 PLAIN HOLES.



'X' VERSION
Ø2.5 PLAIN HOLES

RoHS COMPLIANT
TOLERANCE NO DEC. PLACE ± 1 DEC. PLACE ± 2 DEC. PLACE ± HOLE Ø ± ANGLES ± UNLESS OTHERWISE STATED

Cliff Electronic Components Ltd.

76 Holmesthorpe Avenue, Holmesthorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED
TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2015

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

MATERIAL: SEE NOTES + TABLE

FINISH: SEE NOTES + TABLE

DRAWN: D.P.J.

APPROVED: D.P.J.

3rd ANGLE PROJECTION:



DO NOT SCALE

TITLE: FEED THROUGH FTP CAT6 RJ45 SHIELDED

DRWG. No. CP30222S

FORM: A4DRWGH