




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	JUL 22/19	L.CHAN




FRONT VIEW



SIDE VIEW



BOTTOM VIEW



RECOMMENDED PANEL CUTOUT

MATERIALS:

PLASTIC HOUSING: ENGINEERING THERMOPLASTIC
FLAMMABILITY RATING UL94V-0. COLOUR: BLACK.

CONTACTS:

PHOSPHOR BRONZE
PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES
SEE AMPHENOL PART NUMBER FOR DETAIL.
50 μ" [1.27 MICRONS]
MIN. NICKEL UNDERPLATE.
GOLD FLASH ON CONTACT TAILS.


SHIELD:

COPPER ALLOY
PLATING: NICKEL

PART NUMBER: RJE05-188-3X1C

GOLD PLATING

1 = 6 uINCH
2 = 15 uINCH
3 = 30 uINCH
4 = 50 uINCH



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)
TOLERANCE: ±0.05[.002]

LOCATE HOLES

⌀ 0.13[.005]

POSITION DIMENSIONS
ARE BASIC



UNLESS SPECIFIED OTHERWISE		DRAWN	HANSON.C	DATE	JUL 22/19
PRIMARY UNITS	MILLIMETER	CHECKED	L.CHAN		JUL 22/19
SECONDARY	INCH	M.E. APP'D			
REFERENCE IN PARENTHESES		Q.A. APP'D			
GENERAL TOLERANCES		DWG APPR.	L.CHAN		JUL 22/19
1 DECIMAL PLACE	±0.30	ENG. REL. NO.			
2 DECIMAL PLACES	±0.25	REF.			
3 DECIMAL PLACES	±0.20	THIRD ANGLE PROJECTION			
ANGULAR DEGREES	±1.0°	DO NOT SCALE DRAWING			

Amphenol Canada Corp.			
Commercial Products			
TITLE RJE05 SERIES MODULAR JACK, 8 POSITIONS, 8 CONTACTS, SHIELDED, FRONT PCB TAILS-RoHS COMPLIANT			
DWG. NO.	P-RJE05-188-3X1C		REV A
CODE ID NO.	03554	DWG SIZE:	C
SCALE:	N/A	SHEET	1 OF 1