





Note 1 The tightening torque of Ref. No. 5: 2 to 2.5 N·m.  
Apply Loctite 243 HENKEL JAPAN or equivalent to the threaded portion (M14 $\times$ 0.75) of Ref. No. 1  
in order to prevent loosening.

3	Polyphenylene sulfide	(Black)	6	Phosphor bronze	Nickel plating							
2	Copper alloy	Silver plating 2μm min.	5	Brass	Nickel plating							
1	Zinc alloy	Matte finish nickel plated	4	Polyphenylene sulfide	(Black)							
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS						
UNITS mm				SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.				APPROVED : TP. KOMATSU		20230613		DRAWING NO.		EDC-027511-81-00		
				CHECKED : HY. KOBAYASHI		20230613		PART NO.		RM12BRD-6PH(81)		
				DESIGNED : HT. ZENBA		20230613		CODE NO.		CL0109-0827-9-81		
				DRAWN : KR. SUZUKI		20230613				1/1		