




Note 1 The tightening torque of Ref. No. ⑤: 2 to 2.5 N·m.
Apply Loctite 243 HENKEL JAPAN or equivalent to the threaded portion (M14×0.75) of Ref. No. ① in order to prevent loosening.

3	Polyphenylene sulfide	(Black)	6	Phosphor bronze	Nickel plating
2	Copper alloy	Silver plating 5μm min.	5	Brass	Nickel plating
1	Zinc alloy	Matte finish nickel plated	4	Polyphenylene sulfide	(Black)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-C-00016538	DESIGNED TY. SUZUKI
HIROSE ELECTRIC CO., LTD.		APPROVED : TP. KOMATSU	20230612	DRAWING NO.	EDC-006792-81-00
		CHECKED : HY. KOBAYASHI	20230612	PART NO.	RM12BRD-7S(81)
		DESIGNED : HT. ZENBA	20230609	CODE NO.	CL0109-0619-1-81
		DRAWN : KR. SUZUKI	20230607		