

10		9		8	
ITEM	MOLEX P/N	DESCRIPTION		QTY	UOM
A,B	5051510800	2.0W/B REC HSG 8ckt		2	PC
C	5051520800	2.0W/B RETAINER 8ckt		2	PC
D	5054878000	2.0W/B CRIMP TERM AU PLATING		16	PC
PL	-	PART ID LABEL		1	PC

TABLE 1		
LABEL ID	LABEL CONTENT	REMARK
PL	MOLEX PN MOLEX BATCH WK/YR	LABEL TEXT MUST BE 2MM MAX IN HEIGHT WITH ARIAL FONT AND WRAPPED IN FLAG TYPE ON A SINGLE WIRE.

FROM	TO	WIRE SIZE	WIRE TYPE	COLOR
A-1	B-1	0.22 SQMM	ENDURA	BLACK
A-2	B-2	0.22 SQMM	ENDURA	BLACK
A-3	B-3	0.22 SQMM	ENDURA	BLACK
A-4	B-4	0.22 SQMM	ENDURA	BLACK
A-5	B-5	0.22 SQMM	ENDURA	BLACK
A-6	B-6	0.22 SQMM	ENDURA	BLACK
A-7	B-7	0.22 SQMM	ENDURA	BLACK
A-8	B-8	0.22 SQMM	ENDURA	BLACK




TABLE			
FG PART #	L1	TITLE	
2284252082	150±5	Dura-Clik TPA R-R 8Ckt	150MM disc Au
2284252084	500±5	Dura-Clik TPA R-R 8Ckt	500MM disc Au

NOTE:

1. CONNECTOR VIEW/CIRCUIT NOS SHOWN FROM THE MATING SIDE OF THE CONNECTOR, CONNECTOR VIEW IS SHOWN ONLY FOR REFERENCE. .
2. THE PRODUCT HAS TO MEET PERFORMANCE SPECIFICATION AS PER ES-36586-004.

TESTING REQUIREMENT		
TEST NAME/COMPONENT NAME	TEST PARAMETER	REQUIREMENT
Continuity/Short/Open	AS PER PIN OUT TABLE	100%

A1	FG DESCRIPTION UPDATED	ER	18/02/2025
A	INITIAL RELEASE	804956	21/11/2024
REVISION	CHANGE NOTE	EC NO	DATE
REVISION HISTORY			

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
	DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex			
	mm		NTS									
	GENERAL TOLERANCES (UNLESS SPECIFIED)											
	ANGULAR TOL ± °											
	4 PLACES		±		EC NO: 813242 DRWN: BHARAB5							

DOCUMENT STATUS	P1	RELEASE DATE	2025/02/25	19:42:01
-----------------	----	--------------	------------	----------