

2.92mm ATTENUATORS UP TO **40 GHz**
UP TO **2 WATTS**

2.92mm ATTENUATORS UP TO **40 GHz**
UP TO **2 WATTS**

SPECIFICATIONS:

Electrical:

Electrical:

Frequency Range _____ DC – 40 GHz

Standard Freq. Values _____ 26.5 & 40 GHz

Standard dB Values _____ 0, 3, 6, 10, 20 & 30 dB

Attenuation Accuracy: DC – 26.5 GHz 26.5 – 40 GHz

0, 3 & 6 dB _____ ± 0.5 dB _____ ± 0.8 dB

10 & 20 dB _____ ± 0.6 dB _____ ± 1.0 dB

30 dB _____ ± 0.8 dB _____ ± 1.0 dB

VSWR:

VSWR:

DC	—	18 GHz	_____	1.30:1	Max.
18	—	40 GHz	_____	1.40:1	Max.

Input Power _____ See Below

Impedance _____ 50 Ohms


Operating Temp Range _____ -65°C to $+125^{\circ}\text{C}$

RF Leakage _____ 90 dB Min


Mechanical:

Mechanical:
2.9mm Connectors _____ Passivated Stainless Steel
(Mate both Mechanically & Electrically with
all SMA, K* & 3.5mm Series Connectors.)

Mechanical:
2.9mm Connectors _____ Passivated Stainless Steel
(Mate both Mechanically & Electrically with
all SMA, K* & 3.5mm Series Connectors.)
Conductors _____ Gold Plated Beryllium Copper



WITHOUT HEX



WITH HEX

— 5/16 [7.9] HEX

26.5 GHz Attenuators

dB Value	LENGTH	
	Inches	Millimeters
0 — 12 dB	.88 ±.05	[22.4 ±1.3]
13 — 30 dB	1.01 ±.05	[25.7 ±1.3]

Input Power _____ 2 Watt Avg. @ 25°C
DERATED LINEARLY TO 0.5 WATTS @ +125°C

40 GHz Attenuators

dB Value	LENGTH	
	Inches	Millimeters
0 – 30 dB	.88 ± .05	[22.4 ± 1.3]

Input Power _____ 0.5 Watts Avg. @ 25°C
DERATED LINEARLY TO 0.1 WATTS @ +125°C

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
		DIMENSION UNITS		SCALE		CURRENT REV DESC: RELEASED							
F_A = 0		INCH/MM		NTS									
		GENERAL TOLERANCES (UNLESS SPECIFIED)				molex							
		MM		INCH									
F_C = 0		4 PLACES		±	±	26.5 AND 40GHz 2.92 ATTENUATORS							
		3 PLACES		±	±								
F_P = 0		2 PLACES		±	±	PRODUCT CUSTOMER DRAWING							
		1 PLACE		±	±								
DIVISIONAL SYMBOLS		0 PLACES		±	±	DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
		ANGULAR TOL ± 0.5°				732870300		PSD		000		A	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				C-SIZE		73287		SEE TABLE		GENERAL MARKET		1 OF 2	

* K is a trademark of Anritsu/Wiltron Corp.

