









LF Contacts number	Distance in mm between axes		Length in mm	LF Contacts reference mark number			
	A	B	C	D	E	F	G
004	1,27	8,27	12,87	I	2	3	4
006	2,54	9,54	14,14	I	3	4	6
008	3,81	10,81	15,41	I	4	5	8
010	5,08	12,08	16,68	I	5	6	10
012	6,35	13,35	17,95	I	6	7	12
014	7,62	14,62	19,22	I	7	8	14
016	8,89	15,89	20,49	I	8	9	16
018	10,16	17,16	21,76	I	9	10	18
020	11,43	18,43	23,03	I	10	11	20
022	12,7	19,7	24,3	I	11	12	22
024	13,97	20,97	25,57	I	12	13	24
026	15,24	22,24	26,84	I	13	14	26
028	16,51	23,51	28,11	I	14	15	28
030	17,78	24,78	29,38	I	15	16	30
032	19,05	26,05	30,65	I	16	17	32
034	20,32	27,32	31,92	I	17	18	34
036	21,59	28,59	33,19	I	18	19	36
038	22,86	29,86	34,46	I	19	20	38
040	24,13	31,13	35,73	I	20	21	40
042	25,4	32,4	37	I	21	22	42
044	26,67	33,67	38,27	I	22	23	44
046	27,94	34,94	39,54	I	23	24	46
048	29,21	36,21	40,81	I	24	25	48
050	30,48	37,48	42,08	I	25	26	50
052	31,75	38,75	43,35	I	26	27	52
054	33,02	40,02	44,62	I	27	28	54
056	34,29	41,29	45,89	I	28	29	56
058	35,56	42,56	47,16	I	29	30	58
060	36,83	43,83	48,43	I	30	31	60

Notes:

- "XXX" to be replaced by the number of LF contacts.
- In commercial designation **X** to be replaced by the type of crimp contacts, A or B or G.
- Connector delivered with fittings assembled.
- General tolerance $\pm 0,2$

MICRO HDAS
Female connector
MHDAS 2 F XXX **X** E01



EXPORT CONTROL CLASSIFICATION NOT CONTROLLED/EAR99
Information contained in this document is not subject to Export Control Regulations of the European Union, USA or other countries. Each recipient of this document is responsible for ensuring that transfer or use of any information contained in this document complies with all relevant Export Control regulations and EAR99 regulations.

DRAWN BY : A Samanta		UPDATED BY : S Suryavanshi		LAST APPROVED BY : R Courtin	
ALL DIMENSIONS ARE IN MM		SCALE : 7		ORIGINAL DRAWING DATE : 12/09/2022	
AMPHENOL SOCAPEX		B.P. 29 74311 THYEZ CEDEX		CONFIGURATION DATA ARE AVAILABLE IN PDM	
REV : B		PAGE : 1/1		169-PLC-1739-00	