






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECN-24-276632	08AUG2024	DK	CL

- 1 MATERIAL: SEE TABLE
- 2 RECOMMENDED MATING PART: 2391515-2,2391515-3,2391515-4,2391517-1,2391518-1,2416056-2,2391520-1
- 3 PACKAGING: ON REEL
- 4 REFERENCE CRIMP INFORMATION:
WIRE RANGE: 16-18AWG COPPER STRANDED
INSULATION RANGE:1.95-2.5mm



SECTION C-C
SCALE 10:1



SECTION D-D
SCALE 10:1

TIN PRE-PLATED	BRASS, 0.25 THICK	2406089-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAMBALL SANTOSH 01DEC2023	TE Connectivity	
DIMENSIONS:		CHK OTTO CHEN 01DEC2023		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD DANIEL Z 01DEC2023	NAME TAB TERMINAL 16-18AWG, POWER DOUBLE LOCK	
	0 PLC	±	PRODUCT SPEC	
	1 PLC	±0.40	108-160365	
	2 PLC	±0.30	APPLICATION SPEC	
	3 PLC	±	114-160773	
	4 PLC	±	FINISH	
MATERIAL	-	WEIGHT	-	RESTRICTED TO
SEE TABLE	SEE TABLE	CUSTOMER DRAWING	SIZE A	SCALE 10:1
			CAGE CODE -	SHEET 1 OF 1
			DRAWING NO C=2406089	REV A