





**NOTES:**

1. PARTS TO BE BULK PACKED.
2. CONTACTS ARE SUPPLIED LOOSE.
3. ALL DIMENSIONS ARE FOR REFERENCE ONLY EXCEPT WHERE NOTED WITH TOLERANCE.

**FACE VIEW**HEX NUT  
MAT'L: UV PBT, BLACKGASKET  
MAT'L: RUBBER, BLACK13/16-27 UNS-2A  
MODIFIED THREADPANEL CONNECTOR, FEMALE  
MAT'L: UV PBT, BLACK(3) #12 SOCKET CONTACT  
CRIMP STYLE  
MAT'L: COPPER ALLOY  
GOLD PLATED(4) #26 SOCKET CONTACT  
CRIMP STYLE  
MAT'L: COPPER ALLOY  
GOLD PLATED**WIRE VIEW**

DIMENSIONS IN BRACKETS [ ] ARE METRIC.

**CUSTOMER APPROVAL**

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: \_\_\_\_\_  
DATE: \_\_\_\_\_

**RoHS COMPLIANT**

|                                                                                                                                                |       |          |                                          |                            |
|------------------------------------------------------------------------------------------------------------------------------------------------|-------|----------|------------------------------------------|----------------------------|
| A                                                                                                                                              | MA    | 09-11-24 | RELEASED PER PDR 20013-4                 |                            |
|                                                                                                                                                | AB    | 03-19-21 | DRAWING CREATED PER PDR 20013; P-20013-4 |                            |
| REV.                                                                                                                                           | INIT. | DATE     | DESCRIPTION                              |                            |
| ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED. |       |          | ORIG. DRAWN BY: AB                       | DATE: 03-19-21             |
| ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.                                                                                |       |          | CHECKED BY:                              |                            |
| APPROVED BY:                                                                                                                                   |       |          | APPROVED BY:                             |                            |
| SCALE NTS                                                                                                                                      |       |          | SIZE B                                   | SHEET 1 OF 1               |
| FILE: W4B80-7SG-300                                                                                                                            |       |          | DIRECTORY: SLW                           | PART NUMBER: W4B80-7SG-300 |
| TITLE: PANEL CONNECTOR KIT (3) #12 + (4) #26 SOCKET CONTACTS, CRIMP MULTI-CON-X, WEATHER RESISTANT STANDARD PRODUCT                            |       |          | CUSTOMER: STANDARD PRODUCT               |                            |
| = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX                                                                                                  |       |          | REV A                                    |                            |