








SYSTEM CONFIDENTIAL



DETAIL A
Scale 5



RECOMMENDED PC BOARD LAYOUT
(Component side)



Contact location according to
ISO/IEC 7816-2

- Notes :
- 1 - Termination to PCB : Thru hole tails.
Temperature/time profile according to :
C&K PS-LF-002 specification.
 - 2 - 2,5 microns min tin plating on contact terminal areas and
0,1 microns min gold plating on switch terminal areas.
 - 3 - Contacts forces :
- max 0,5 N per contact with max. card thickness.
- min 0,2 N per contact with min. card thickness.

- 4 - Card end travel switch NO activates when the
sliding card is 1 mm from the card stop.
- 5 - For packaging on tray, see document :
cu 030278Y0041.
- 6 - In case of customer accessories integration
requesting an interface with CCM, please ask
C&K for a 3D model.

MATIERE		TRAITEMENT		PROTECTION	
SAUF INDIQUE : -COTES DONNEES AVANT PROTECTION -BAVURES ET ARETES VIVES SUPPRIMEES		TOL. LINEAIRE	± 0,1	TOL. ANGULAIRE	± 2
DESSINE		DATE	28-11-08	ANALYSE	Y
VERIFIE		DATE	02/12/2008	TAB. FAM.	Y
APPROUVE		DATE	02/12/2008	PRO/E	Y
L. BOUVIER		REMPLECE		LANGAGE	
G. PINON		DESIGNATION		E	
L. KUBAT		PROJECTION 1ER DIEDRE		CCM02-F503LFT	
C&K Components		ECHELLE		Sliding version	
BP 359 - 39105 Dole - FRANCE -		TAILLE		4 clips for 1,6 mm PCB	
		FEUILLE		1122M1YF503	
		NUMERO		REV	
		A3		CU	