

HOW TO REQUEST NEW PLATE CONFIGURATIONS
(SEE PART NUMBER TABLE FOR CURRENT RELEASED PLATES)
STANDARD (SHEET 2) OR HIGH DENSITY (SHEET 3) SPACING
RoHS YES (SILVER PLATING)/NO (TIN PLATING)
NUMBER OF ROWS
NUMBER OF LINES PER ROW (PLATE SIZE RESTRICTED, SEE SHEETS 2+3)
FILTER DESIGNATION (SEE FILTER DESIGNATION TABLE)
PLATE LENGTH (SEE TABLES ON SHEETS 2 + 3)
LEAD CONFIGURATION PER SHEETS 2 + 3: STRAIGHT (0), LEFT (1), RIGHT (2), BOTH (3)
SELECTIVE LINE FILTERING ALSO AVAILABLE, CONTACT MOLEX FOR CUSTOM CONFIGURATIONS


FILTER DESIGNATION SELECTION TABLE

Filter Designation	Filter*** Circuits	Capacitance		3 dB Max Cut-of Frequency (MHz)	Working Voltage DC -55°C to +125°C	Minimum Insertion Loss - Decibels (dB) 50ohm system per MIL-STD-220 (no load)							
		Value	Tolerance			5 MHZ	10 MHZ	20 MHZ	50 MHZ	100 MHZ	200 MHZ	500 MHZ	1 GHZ
A	C	68pF	+/-25%	73.9	100V	-	-	-	-	-	3	10	16
B	C	100pF	+/-25%	50.3	100V	-	-	-	-	1	6	13	19
C	C	135pF	+100/-0%	23.3	100V	-	-	-	1	5	10	16	20
D	C	470pF	+/-25%	10.7	100V	-	-	2	7	13	18	25	27
E	C	820pF	+/-25%	6.2	100V	-	1	5	12	18	23	30	33
F	C	1000pF	+/-25%	5.1	100V	-	2	7	14	20	25	32	35
G	C	1500pF	+/-25%	3.4	100V	1	4	10	16	22	29	36	37
H	C	2500pF	+100/-0%	1.26	100V	5	11	17	23	29	35	38	40
I	C	4000pF	+100/-0%	0.8	100V	9	15	21	27	34	38	42	46
J	Insulated	10pF	Max.	635	100V	-	-	-	-	-	-	-	-
K	Grounded					-	-	-	-	-	-	-	-
L	Pi	68	+/-25%	65.3	100V	-	-	-	-	1	3	8	19
M	Pi	100	+/-25%	45.1	100V	-	-	-	-	2	6	11	27
N	Pi	135	+100/-0%	22.0	100V	-	-	-	1	6	10	20	34
O	Pi	470	+/-25%	10.6	100V	-	-	-	8	14	21	36	43
P	Pi	820	+/-25%	6.2	100V	-	-	4	13	22	31	45	52
Q	Pi	1000	+/-25%	5.1	100V	-	2	6	14	22	33	51	59
R	Pi	1700	+100/-0%	1.9	100V	1	6	12	23	35	48	64	69
S	Pi	2500	+100/-0%	1.3	50V	4	9	15	28	41	54	70	70
T	Pi	5000	+100/-0%	0.65	100V	9	15	23	41	53	66	70	70

*** FOR HIGH DENSITY FILTER PLATES (2mm CENTERS) ONLY C STYLE FILTERS ARE AVAILABLE


NOTES:

1. MATERIALS:
 - PLATE: BRASS PER UNS C26000/C27000
 - LEADS: COPPER ALLOY
2. PLATING:
 - PLATE:
 - RoHS COMPLIANT: SILVER
 - NON-RoHS COMPLIANT: MATTE TIN
 - LEADS: GOLD
3. PLATES MARKED WITH: MOLEX. MOLEX P/N AND DATE CODE IN YYWW FORMAT



FUNCTIONAL SYMBOLS F_A = 0 F = 0 F_D = 0 DIVISIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT PERMISSION																	
		DIMENSION UNITS		SCALE		CURRENT REV DESC: RELEASED													
		INCH/mm		NTS															
		GENERAL TOLERANCES (UNLESS SPECIFIED)				molex BOLT-IN FILTER PLATES PRODUCT CUSTOMER DRAWING <table><tr><td>DOCUMENT NUMBER</td><td>DOC TYPE</td><td>DOC PART</td><td>REVISION</td></tr><tr><td>732860010</td><td>PSD</td><td>000</td><td>A</td></tr></table>						DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION	732860010	PSD	000	A
		DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION														
		732860010	PSD	000	A														
				MM								INCH							
		4 PLACES		±	±														
		3 PLACES		±	±														
		2 PLACES		±	±														
1 PLACE		±	±																
0 PLACES		±	±																
ANGULAR TOL				± 0.5°		STATUS: Production DRWN: Kevin Tagan2024-08-20 CHK'D: Les Meier2024-08-20 APPR: James Borrelli2024-08-20													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION						DRAWING		SERIES							
				C-SIZE						73286									

Plate length (A)	No. of filtered lines per row	STANDARD DENSITY	
		B	C
1.060* (26.92)	1	0 (0.00)	0.53 (13.46)
	2	0.1 (2.54)	0.43 (10.92)
	3	0.2 (5.08)	0.43 (10.92)
	4	0.3 (7.62)	0.33 (8.38)
	5	0.4 (10.16)	0.33 (8.38)
1.560* (39.62)	1	0 (0.00)	0.73 (18.54)
	2	0.1 (2.54)	0.73 (18.54)
	3	0.2 (5.08)	0.63 (16.00)
	4	0.3 (7.62)	0.63 (16.00)
	5	0.4 (10.16)	0.53 (13.46)
	6	0.5 (12.70)	0.53 (13.46)
	7	0.6 (15.24)	0.43 (10.92)
	8	0.7 (17.78)	0.43 (10.92)
	9	0.8 (20.32)	0.33 (8.38)
	10	0.9 (22.86)	0.33 (8.38)
2.560 (65.02)	5	0.4 (10.16)	1.03 (26.16)
	6	0.5 (12.70)	1.03 (26.16)
	7	0.6 (15.24)	0.93 (23.62)
	8	0.7 (17.78)	0.93 (23.62)
	9	0.8 (20.32)	0.83 (21.08)
	10	0.9 (22.86)	0.83 (21.08)
	11	1.0 (25.40)	0.73 (18.54)
	12	1.1 (27.94)	0.73 (18.54)
	13	1.2 (30.48)	0.63 (16.00)
	14	1.3 (33.02)	0.63 (16.00)
	15	1.4 (35.56)	0.53 (13.46)
	16	1.5 (38.10)	0.53 (13.46)
	17	1.6 (40.65)	0.43 (10.92)
	18	1.7 (43.18)	0.43 (10.92)
	19	1.8 (45.72)	0.33 (8.38)
	20	1.9 (48.26)	0.33 (8.38)
3.560 (90.42)	13	1.2 (30.48)	1.13 (27.70)
	14	1.3 (33.02)	1.13 (27.70)
	15	1.4 (35.56)	1.03 (26.16)
	16	1.5 (38.10)	1.03 (26.16)
	17	1.6 (40.65)	0.93 (23.62)
	18	1.7 (43.18)	0.93 (23.62)
	19	1.8 (45.72)	0.83 (21.08)
	20	1.9 (48.26)	0.83 (21.08)
	21	2.0 (50.80)	0.73 (18.54)
	22	2.1 (53.34)	0.73 (18.54)
	23	2.2 (55.88)	0.63 (16.00)
	24	2.3 (55.42)	0.63 (16.00)
	25	2.4 (60.96)	0.53 (13.46)
	26	2.5 (63.50)	0.53 (13.46)
	27	2.6 (66.04)	0.43 (10.92)
	28	2.7 (68.58)	0.43 (10.92)
	29	2.8 (71.12)	0.33 (8.38)
	30	2.9 (73.66)	0.33 (8.38)



FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIVISIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC: RELEASED				molex BOLT-IN FILTER PLATES					
		INCH/mm		NTS											
		GENERAL TOLERANCES (UNLESS SPECIFIED)													
		MM		INCH											
		4 PLACES		±										±	
		3 PLACES		±						±					
		2 PLACES		±						±					
1 PLACE		±		±		STATUS: Production DRWN: Kevin Tagan 2024-08-20 CHK'D: Les Meier 2024-08-20 APPR: James Borrelli 2024-08-20									
0 PLACES		±		±											
ANGULAR TOL		± 0.5°													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
				C-SIZE		73286		SEE TABLE		GENERAL MARKET		2 OF 4			
								DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
								732860010		PSD		000		A	

* 1.060 (26.92) AND 1.560 (39.62) LONG PLATES DO NOT HAVE COINING. INCREASE THESE DIMENSIONS BY .020 (0.51) IF USING THESE SIZED PLATES

** DIMENSION NOT APPLICABLE FOR SINGLE ROW DESIGNS

HOW TO REQUEST NEW PLATE CONFIGURATIONS
(SEE PART NUMBER TABLE FOR CURRENT RELEASED PLATES)

- STANDARD (SHEET 2) OR HIGH DENSITY (SHEET 3) SPACING
- RoHS YES (SILVER PLATING)/NO (TIN PLATING)
- NUMBER OF ROWS
- NUMBER OF LINES PER ROW (PLATE SIZE RESTRICTED, SEE SHEETS 2+3)
- FILTER DESIGNATION (SEE FILTER DESIGNATION TABLE)
- PLATE LENGTH (SEE TABLES ON SHEETS 2 + 3)
- LEAD CONFIGURATION PER SHEETS 2 + 3: STRAIGHT (0), LEFT (1), RIGHT (2), BOTH (3)

SELECTIVE LINE FILTERING ALSO AVAILABLE, CONTACT MOLEX FOR CUSTOM CONFIGURATIONS


FILTER DESIGNATION SELECTION TABLE

Filter Designation	Filter*** Circuits	Capacitance		3 dB Max Cut-of Frequency (MHz)	Working Voltage DC -55°C to +125°C	Minimum Insertion Loss - Decibels (dB) 50ohm system per MIL-STD-220 (no load)							
		Value	Tolerance			5 MHZ	10 MHZ	20 MHZ	50 MHZ	100 MHZ	200 MHZ	500 MHZ	1 GHZ
A	C	68pF	+/-25%	73.9	100V	-	-	-	-	-	3	10	16
B	C	100pF	+/-25%	50.3	100V	-	-	-	-	1	6	13	19
C	C	135pF	+100/-0%	23.3	100V	-	-	-	1	5	10	16	20
D	C	470pF	+/-25%	10.7	100V	-	-	2	7	13	18	25	27
E	C	820pF	+/-25%	6.2	100V	-	1	5	12	18	23	30	33
F	C	1000pF	+/-25%	5.1	100V	-	2	7	14	20	25	32	35
G	C	1500pF	+/-25%	3.4	100V	1	4	10	16	22	29	36	37
H	C	2500pF	+100/-0%	1.26	100V	5	11	17	23	29	35	38	40
I	C	4000pF	+100/-0%	0.8	100V	9	15	21	27	34	38	42	46
J	Insulated	10pF	Max.	635	100V	-	-	-	-	-	-	-	-
K	Grounded					-	-	-	-	-	-	-	-
L	Pi	68	+/-25%	65.3	100V	-	-	-	-	1	3	8	19
M	Pi	100	+/-25%	45.1	100V	-	-	-	-	2	6	11	27
N	Pi	135	+100/-0%	22.0	100V	-	-	-	1	6	10	20	34
O	Pi	470	+/-25%	10.6	100V	-	-	-	8	14	21	36	43
P	Pi	820	+/-25%	6.2	100V	-	-	4	13	22	31	45	52
Q	Pi	1000	+/-25%	5.1	100V	-	2	6	14	22	33	51	59
R	Pi	1700	+100/-0%	1.9	100V	1	6	12	23	35	48	64	69
S	Pi	2500	+100/-0%	1.3	50V	4	9	15	28	41	54	70	70
T	Pi	5000	+100/-0%	0.65	100V	9	15	23	41	53	66	70	70

*** FOR HIGH DENSITY FILTER PLATES (2mm CENTERS) ONLY C STYLE FILTERS ARE AVAILABLE

NOTES:

1. MATERIALS:
 - PLATE: BRASS PER UNS C26000/C27000
 - LEADS: COPPER ALLOY
2. PLATING:
 - PLATE:
 - RoHS COMPLIANT: SILVER
 - NON-RoHS COMPLIANT: MATTE TIN
 - LEADS: GOLD
3. PLATES MARKED WITH: MOLEX. MOLEX P/N AND DATE CODE IN YYWW FORMAT



FUNCTIONAL SYMBOLS F_A = 0 F = 0 F_D = 0 DIVISIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT PERMISSION																							
		DIMENSION UNITS		SCALE		CURRENT REV DESC: RELEASED																			
		INCH/mm		NTS																					
		GENERAL TOLERANCES (UNLESS SPECIFIED)																							
			MM	INCH																					
		4 PLACES	±	±																					
		3 PLACES	±	±																					
		2 PLACES	±	±																					
		1 PLACE	±	±																					
		0 PLACES	±	±																					
ANGULAR TOL				0.5°														STATUS: Production DRWN: Kevin Tagan2024-08-14 CHK'D: Les Meier2024-08-19 APPR: James Borrelli2024-08-19							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER											
				C-SIZE		73287		SEE TABLE		GENERAL MARKET		1 OF 4													

molex				
BOLT-IN FILTER PLATES				
PRODUCT CUSTOMER DRAWING				
DOCUMENT NUMBER 732870010		DOC TYPE PSD	DOC PART 000	REVISION A

