




THIS DOCUMENT CONTAINS Aavid THERMALLOY'S INTELLECTUAL PROPERTY WHICH IS SUPPLIED IN CONFIDENCE; IT MUST NOT BE USED FOR ANY PURPOSE OTHER THAN WHICH IT IS SUPPLIED; IT MUST NOT BE REPRODUCED WITHOUT WRITTEN PERMISSION FROM THE OWNERS



NOTES:

1- MATERIAL: BRASS

2- FINISH: ELECTRO TIN PLATE


ORDER CODE 406069: Ni PLATED; ELECTROLYTIC TINNING THICKNESS MIN. 5 MICRON

ORDER CODE 406069G: 0.002-3 mm Ni UNDERCOAT; 0.005±0.001 mm MATT Sn

MATT Sn CONSIDERED (AS PER NEMI) TO BE: GRAIN=0.001-5 mm; CARBON=0.005-0.05%

3- SOLDERABILITY TO ATI 07.5.24

4- MUST BE BURR FREE



**AAVID THERMALLOY**

EUROPE [www.aavidthermalloy.com](http://www.aavidthermalloy.com)

Via XXV Aprile, 32 Cheney Manor  
40057 Cadriano - Bologna ITALY SWINDON WILTS SN2 2QN UK  
Tel. +39 051 764011 Tel. +44 1793 401400  
Fax +39 051 764090 Fax +44 1793 615396

COMPANY WITH QUALITY SYSTEM CERTIFIED BY LRQA ISO 9001:2000

Die n.	MATERIAL See notes				DRAWING n.	<b>BM016</b>	
Factor	GENERAL TOLERANCES				Vis. n.		
Perim.	MACHINING UNI 2768 M				Description:	PIN-BRASS-D.4x10.8 -ST.1-TIN-BM016 B	
Area	FINISH				Format	Scale	1 ⊕
Weight	See notes				By	A4	10 : 1
Note:	P/N before treatment P/N prima del trattamento 406047	Drawn A. Montaguti	B	13Jan05	RoHS plating details added ECF 333 B0 refers	AS	
		Check	A	18Jan02	ORIGINAL (was R400016)		
REV	Date				Revision description		