


9		8		7		6		5		4		3		2		1	
Molex Finished Good Part Number	Molex Sub-assy Part Number	DIM A Overall Length (in[mm])	Braid Type	Approx. Circular Mils	Ampacity Max	Approx. AWG Equivalent	DIM B Terminal Width in[mm])	DIM C Terminal Thickness (in[mm])	DIM D Terminal Length (in[mm])	DIM E Terminal Hole Dia (in[mm])	DIM F C/L of Terminal Hole (in[mm])	DIM G Bend Height (in[mm])	DIM H Bend Radius (in[mm])	DIM J Heat Shrink Width (in[mm])	DIM K Heat Shrink Thickness (in[mm])		
2076025047	2076025032	6.0 [152]	24x5/30	12060	53	10	.540 [13.72]	.080 [2.03]	.520 [13.21]	.203 [5.16]	.260 [6.60]	.680 [17.27]	.080 [2.03]	.42 [10.7]	.10 [2.5]		
2076025048	2076025033	12.0 [305]															
2076025049	2076025034	18.0 [457]															
2076025050	2076025035	24.0 [607]															
2076025051	2076025036	36.0 [914]															
2076025052	2076025037	6.0 [152]	48x24/36	28800	105	6	.750 [19.05]	.095 [2.41]	.750 [19.05]	.281 [7.14]	.375 [9.53]	.940 [23.87]	.095 [2.41]	.79 [20.0]	.12 [3.0]		
2076025053	2076025038	12.0 [305]															
2076025054	2076025039	18.0 [457]															
2076025055	2076025040	24.0 [607]															
2076025056	2076025041	36.0 [914]															
2076025057	2076025042	6.0 [152]	48x14/30	67200	150	2	1.00 [25.4]	.120 [3.05]	1.00 [25.4]	.406 [10.31]	.500 [12.70]	1.240 [31.50]	.120 [3.05]	1.04 [26.4]	.16 [4.0]		
2076025058	2076025043	12.0 [305]															
2076025059	2076025044	18.0 [457]															
2076025060	2076025045	24.0 [607]															
2076025061	2076025046	36.0 [914]															



NOTES:

- MATERIAL:
FERRULES - COMPRESSED SEAMLESS COPPER TUBE
BRAID - ELECTRO-PLATED TIN COPPER
HEAT SHRINK TUBING - VW-1, 600V, 125°, COLOR: BLACK
- .005 [0.13] MAX BURR ON ALL SURFACES
- MOLEX LOGO "MX" SHALL BE STAMPED INTO THE PART, LOCATED APPROXIMATELY AS SHOWN AND BE LEGIBLE.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
DIMENSION UNITS	SCALE
HYBRID	1:2
GENERAL TOLERANCES (UNLESS SPECIFIED)	
ANGULAR TOL	± °
4 PLACES	±
3 PLACES	±
2 PLACES	±
1 PLACE	±
0 PLACES	±
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION

CURRENT REV DESC:	
EC NO: 761791	2023/08/29
DRWN: JACOBP9	2023/09/05
CHK'D: TGREGORI	2023/09/05
APPR: MCOLE	2023/09/05
INITIAL REVISION:	
DRWN: TGREGORI	2022/02/08
APPR: JJONIAK	2022/03/30
B-SIZE	207602

molex	
FLEXIBLE BRAIDED R/A TO FLT GRND JUMPERS WITH INSULATION	
PRODUCT CUSTOMER DRAWING	
DOCUMENT NUMBER	DOC TYPE
2076020003-SD	PSD
DOC PART	REVISION
000	B1
MATERIAL NUMBER	CUSTOMER
SEE TABLE	GENERAL MARKET
SHEET NUMBER	1 OF 1

DOCUMENT STATUS	P1	RELEASE DATE	2023/09/05	16:49:09
-----------------	----	--------------	------------	----------