





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		C	EC 0G3B 0215 05	17SEP05	BSV	RCJ



1. 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
2. WIRE RANGE: .5–2mm² [20–14 AWG].
INSULATION RANGE: 1.52–3.30[.060–.130] DIA.
3. DIMENSIONS IN BRACKETS ARE IN INCHES.
4. 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN IN TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.



SECTION A–A
SCALE 10:1



SECTION B–B
SCALE 10:1

GOLD 4	0.30 [.012] PH BRZ	1–770251–0
GOLD 1	0.30 [.012] PH BRZ	770251–4
PRE–TIN	0.30 [.012] PH BRZ	770251–3
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. SALMON 20JAN93	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105–3608	
DIMENSIONS: mm [INCHES]		CHK R. SWING 20JAN93		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. TRULL 01APR93	NAME SOCKET, LOOSE PIECE, UNIVERSAL MATE–N–LOK(TM) II	
MATERIAL SEE TABLE		PRODUCT SPEC APPLICATION SPEC WEIGHT –	SIZE A2	CAGE CODE 00779
FINISH SEE TABLE		CUSTOMER DRAWING	DRAWING NO C=770251	RESTRICTED TO –
		SCALE 4:1	SHEET 1 of 1	REV C

METRIC