


#### MCL239AGW

	REVISIONS					·		·
ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	Α	RELEASED	Veena	25/6/08	Suresh	25/6/08	G. C	10/7/08



### **Specifications:**

Dice material : GaAsP on GaP/GaP.
Emitted color : Orange/green.
Lens color : White diffused.
Peak wavelength : 635/568nm.
Viewing angle : 120 degrees.
Luminous intensity (IV) : 3.2/3.1mcd.



# Electrical/Optical Characterisitics at T<sub>a</sub> = 25°C

Parameter	Symbol	Minimum	Typical	Maximum	Unit	Test
Luminous Intensity	IV	1.5/1.4	3.2/3.1	5.0/4.9	mcd	IF = 20mA
Viewing Angle	20 1/2	-	120	-	degrees	- IF = 2011IA
Peak Emission Wavelength	• p	-	635/568	-		-
Dominant Wavelength	• 10	-	627/570	-	nm	-
Spectral Line Half-Width	Δλ	-	45/30	-		-
Forward Voltage	VF	1.6/1.7	2.0/2.1	2.6/2.6	V	IF = 20mA
Power Dissipation	Pd	-	-	85	-	-
Peak Forward Current (Duty 1/10 at 1KHz)	IF (Peak)	-	-	100	-	-
Recommended Operating Current	IF (Rec)	-	20	-	mA	-

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its regilgence. SPC MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2008.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Veena	25/06/08
CHECKED BY:	DATE:
Suresh	25/06/08
APPROVED BY:	DATE:
G.Cook	10/07/08

DRAWING TITLE:

SIZE	DWG NO.	M10001262		TRONIC FII AGW_DWO			REV A
SCALE: NTS		U.O.M.: mm (Inches)	s) SHEET: 1		1	OI	F 5




MCL239AGW


REVISIONS								
ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	Α	RELEASED	Veena	25/6/08	Suresh	25/6/08	G. C	10/7/08

## Absolute Maximum Ratings ( $T_a = 25$ °C)

Reverse Voltage	5 Volt
Reverse Current	10μA (V <sub>R</sub> = 5V)
Operating Temperature Range	-40°C to 85°C
Storage Temperature Range	-40°C to 100°C
Lead Soldering Temperature Range 1.6mm (1/16 inch) from body	260°C for 5 Seconds

## Orange (GaAsP/CaP $\lambda$ P = 635nm)





This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from engligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group is liability for death or personal injury resulting from its regilgence. SPC MULTICOMP is the registered trademark of the Group. © Premier Fameli pic 2008.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Veena	25/06/08
CHECKED BY:	DATE:
Suresh	25/06/08
APPROVED BY:	DATE:
G.Cook	10/07/08

DRAWING TITLE:


SIZE A	DWG NO.	M10001262		TRONIC FII			REV A
SCALE: NTS		U.O.M.: mm (Inches)	SHEET: 2		2	OF	F 5




MCL239AGW


		REVISIONS						
ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	Α	RELEASED	Veena	25/6/08	Suresh	25/6/08	G. C	10/7/08

## Orange (GaAsP/CaP $\lambda$ P = 635nm)





**Luminous Intensity vs. Ambient Temperature** 



This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its regiligences. SPC MULTICOMP is the registered trademark of the Group. © Premier Farnell pic 2008.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Veena	25/06/08
CHECKED BY:	DATE:
Suresh	25/06/08
APPROVED BY:	DATE:
G.Cook	10/07/08

DRAWING TITLE:


SIZE A	DWG NO.	M10001262	l -	TRONIC FIL			REV A
SCALE: NTS		II O M · mm (Inches)		SHEET	3	ΩF	5





MCL239AGW


	REVISIONS							
ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	Α	RELEASED	Veena	25/6/08	Suresh	25/6/08	G. C	10/7/08

### Green (GaP $\lambda$ P = 568nm)









Luminous Intensity vs. Ambient Temperature

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC MULTICOMP is the registered trademark of the Group. © Premier Farnell ple 2008

TOLERANCES: UNLESS OTHERWISE

SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:	DATE:
Veena	25/06/08
CHECKED BY:	DATE:
Suresh	25/06/08
APPROVED BY:	DATE:
G.Cook	10/07/08


DRAWING TITLE:

SIZE <b>A</b>	DWG NO.	M10001262	ELECTRONIC FILE L239AGW_DWG				REV A
SCALE: NTS		U.O.M.: mm (Inches)		SHEET:	4	OF	5



MCL239AGW

		REVISIONS						
ECN #         REV         DESCRIPTION           -         A         RELEASED		DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
		Veena	25/6/08	Suresh	25/6/08	G. C	10/7/08	



#### **Part Number Table**

Description	Part Number
LED, 2mm x 5mm, Orange/Green	MCL239AGW

http://www.farnell.com

http://www.newark.com

http://www.cpc.co.uk

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its regilgence. SPC MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2008.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

**TOLERANCES:** 

DRAWN BY:	DATE:
Veena	25/06/08
CHECKED BY:	DATE:
Suresh	25/06/08
APPROVED BY:	DATE:
G.Cook	10/07/08

DRAWING TITLE:

2.0mm x 5.0mm x 7.0mm Multi-color LED Lamp-Orange/Green

SIZE A	DWG NO.	M10001262	ELECTRONIC FILE L239AGW_DWG				REV A
SCALE: NTS		U.O.M.: mm (Inches)		SHEET:	5	OF	5