


20	(75.29±0.41)	(79.15±0.51)
	2.964±.016	3.116±.020
19	(71.32±0.41)	(75.18±0.51)
	2.808±.016	2.960±.020
18	(67.36±0.36)	(71.22±0.46)
	2.652±.014	2.804±.018
17	(63.40±0.36)	(67.26±0.46)
	2.496±.014	2.648±.018
16	(59.44±0.36)	(63.29±0.46)
	2.340±.014	2.492±.018
15	(55.47±0.3)	(59.33±0.41)
	2.184±.012	2.336±.016
14	(51.51±0.3)	(55.37±0.41)
	2.028±.012	2.180±.016
13	(47.55±0.30)	(51.41±0.41)
	1.872±.012	2.024±.016
12	(43.59±0.25)	(47.45±0.36)
	1.716±.010	1.868±.014
11	(39.62±0.25)	(43.48±0.36)
	1.560±.010	1.712±.014
10	(35.66±0.25)	(39.52±0.3)
	1.404±.010	1.556±.012
9	(31.70±0.18)	(35.56±0.3)
	1.248±.007	1.400±.012
8	(27.74±0.18)	(31.60±0.3)
	1.092±.007	1.244±.012
7	(23.77±0.18)	(27.64±0.3)
	.9360±.007	1.088±.012
6	(19.81±0.13)	(23.67±0.25)
	.7800±.005	.9320±.011
5	(15.85±0.13)	(19.71±0.25)
	.6240±.005	.7760±.010
4	(11.89±0.13)	(15.75±0.25)
	.4680±.005	.6200±.010
3	(7.92±0.13)	(11.79±0.25)
	.312±.005	.4640±.010
No OF CCTS	DIM. 'A'	DIM. 'B'



- NOTES:
1. THESE ASSEMBLIES STACKABLE END TO END ON (3.96)/.156 CENTRE TO CENTRE PROGRESSION.
 2. FOR CHARTS & PANEL DRILLING DETAILS SEE SHEET 2 AND SUBSEQUENT SHEETS.
 3. TERMINAL PULL OUT FORCE- 4lbs MIN.
 4. TERMINALS ARE LUBRICATED WITH MXI-3.
 5. CONNECTORS FOR USE WITH (1.14)/.045 SQ. OR RD. PINS
 6. THIS PART CONFORMS TO PROD.SPEC.99020-0087

TERMINAL STYLE → A

HOUSING STYLE ↓ C

CR

H

HR

L

LR

REVISION UP-DATE
E2004-0792
P:HEAHN 04/03/08

25
36
1/2

ZB

B

WITH RAMP

WITH HOOKS

WITH HOOKS & RAMP

WITH LOCKS

WITH LOCKS & RAMP

4 : 1 x

G. HART 24/11/82

M GOONEY 26/11/98

MWILHITE 26/11/98

SE32151 .DGN SEE CHART SDAE-3215-***N*** I OF II

C

DIM 'C'

SEE CHART
SDAE-3215-***N*** I OF II

(2.5)
.10

30°

WITH RAMP

WITH HOOKS

WITH HOOKS & RAMP

WITH LOCKS

11 ZA
10 Z
9 Z
8 Z
7 Z
6 Z
5 ZA
4 ZA
3 ZA
2 Y
1 ZB

x

CONNECTOR, K-K (3.96)/.156 WITH OR WITHOUT LOCKING WITH P.C. TAIL TERMINALS

SHT. 1 OF 1			MRI - SDAE-3215-***N***		
MODIFICATION RECORD INDEX					
ECN	ISS.	DATE	INIT.	SHTS. AFFECTED	DESCRIPTION OF MOD.
MESL-077	F	2 .12.82	GH	ALL	REDRAW
MEML-112	G	26.4 .83	GH	ALL	REVISION
MEML-594	H	6 .6 .83	GH	ALL	VARIOUS
MEML-608	J	21.6 .83	GH	ALL	VARIOUS
MEML-681	K	31.8 .83	MAL	ALL	VARIOUS
MEML-901	L	25.6 .84	MC	ALL	VARIOUS
MEML-382	M	2 .10.84	MC	ALL	VARIOUS
MEML-509	N	29.5 .85	MC	ALL	VARIOUS
MEML-510	P	31.5 .85	MC	ALL	VARIOUS
MEML-1162	R	25.11.85	JP	ALL	VARIOUS
MEML-617	S	9 .1.86	MC	ALL	VARIOUS
MEML-625	T	20.1.86	MC	ALL	VARIOUS
E10010	U	11.1.91	POB	ALL	VARIOUS
E10018	V	18.1.91	POB	ALL	VARIOUS
E50203	W	08.12.94	JS	ALL	VARIOUS
E90137	Y	1.11.98	TM	ALL	REDRAWN ON CAD
E2001-0463	Z	1.11.00	MF	1,3,4,5,6,7,8,9,10,11	UPDATED BORDER
E2003-0992	ZA	03.05.29	PS	I	NEW PROD.SPEC.99020-0087 ADDED
MOLEX EUROPE			REVISE ONLY ON CAD SYSTEM		
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. & SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			CADDWG FILENAME		ISSUE
MF00028			SE32151 . DGN		ZA

