

HONEYWELL PART NUMBER
1SX12-T
PRODUCT CODE VDA1250

REV	DOCUMENT	CHANGED BY	CHECK
8	0038446	KVB 20MAY08	BLR



B

A

A


B

A



NOTE -
1-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188 ± .002 CENTERS
2-TERMINALS ARE PLATED FOR SOLDERING
3-SWITCH WILL WITHSTAND TEMPERATURE OF 250° F

RELEASE NO.	SR - 10080
REPLACES	(M) 1SX12-T ISSUE 2

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 		DRAWN	VK	28FEB08	Honeywell					
OPERATING FORCE - - - - 5 OZ MAX		CONTACT ARRANGEMENT SPDT					CHECK	RJ	28FEB08					TITLE SWITCH - BASIC	
RELEASE FORCE- - - - 1 OZ MIN		28 VOLTS DC RATING					0.030 0.015 0.005 THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		SIZE	TYPE	DRAWING NAME		
DIFFERENTIAL TRAVEL- - - .002 MAX		INDUCTIVE			B	I					1SX12-T	8			
OVERTRAVEL - - - - - .004 MIN		RESISTIVE			RASTER						SCALE	-	WEIGHT .003 LB MAX	SHEET 1 OF 1	
		250 VAC 4 AMP													
		UL, CSA			7A, 250 VAC  			BRAND L7							