

FED. MFG. CODE 91929

CATALOG LISTING

SWITCH – BASIC

1H1M1

M

DRAWING
NUMBER

END

5

REVISIONS

A C032230

SRH

B C071228

DAW

C 0082984

DLT
17 MAY 65

17 MAY 58	
-----------	--

REPLACES

RELEASE NO.


CHECK

CHECK

73 CHECK

S R H	10 AUG
-------	--------

FO-52848



NOTE -

- ⚠ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
- 2 - FOR USE IN TEMPERATURE RANGE -300°F TO +250°F
 - 3 - HERMETICALLY SEALED (METAL-TO-METAL, GLASS-TO-METAL)
 - 4 - ALL EXPOSED PARTS ARE OF CORROSION RESISTANT MATERIALS
 - 5 - TERMINALS ARE TINNED FOR SOLDERING
 - 6 - DO NOT APPLY MORE THAN 1 1/2 INCH-LBS OF TORQUE WHEN TIGHTENING MOUNTING SCREWS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA			SCALE 2 TO 1
OPERATING FORCE-----7 OZ MAX	CONTACT ARRANGEMENT S P D T			DO NOT SCALE PRINT
RELEASE FORCE-----1 OZ MIN	LINE VOLTAGE	INDUCTIVE LOAD	RESISTIVE LOAD	UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES TOLERANCES ARE
DIFFERENTIAL TRAVEL-----.006 MAX	28 VDC	3 AMP	5 AMP	ONE PLACE (.01) ± .030
OVERTRAVEL-----.003 MIN	115 VAC (400 CYCLE)	2 AMP	2 AMP	TWO PLACE (.001) ± .015
				THREE PLACE (.000) ± .005
				ANGLES ±
				WEIGHT .014 LB MAX