

HONEYWELL
PART NUMBER


11SM144

PRODUCT CODE

TWV4400

REV	DOCUMENT	CHANGED BY	CHECK
8	0038223	SSK 17APR08	BLR

PLASTIC PLUNGER.



NOTE-

- △ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX. DIA. ON .375^{±.002} CENTERS.**
- 2- TERMINALS ARE PLATED FOR SOLDERING.**
- 3- SWITCH WILL WITHSTAND TEMPERATURE OF 250°F.**

RELEASE NO. SR - 7853

REPLACES -

CHARACTERISTICS

OPERATING FORCE - - - - 3 OZ MAX

RELEASE FORCE - - - - 1 OZ MIN

DIFFERENTIAL TRAVEL - - .002 MAX

OVERTRAVEL - - - - .005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
SPDT

30 VOLTS DC RATING

	SEA LEVEL	50,000 FT
INDUCTIVE	3 AMP	2.5 AMP
RESISTIVE	5 AMP	5 AMP

MAXIMUM INRUSH 24 AMP

APPROVALS	KEMA, CE	5A, 250V ~ T85 1E4	UL, CSA	5A, 250 VAC

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACE	X	±
ONE PLACE	.X	±
TWO PLACE	.XX	±
THREE PLACE	.XXX	±
FOUR PLACE	.XXXX	±
ANGLES		±

THIRD ANGLE PROJECTION



DRAWN

VK

27 NOV 07

CHECK

RJ

27 NOV 07

THIS DRAWING COVERS A PROPRIETARY ITEM
AND IS THE PROPERTY OF HONEYWELL.
THIS DRAWING IS NOT TO BE COPIED OR USED
WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ANSI Y14.5M-1982
OTHER HONEYWELL ENGINEERING
STANDARDS MAY APPLY

RASTER

Honeywell

TITLE

SWITCH - BASIC

SIZE

B

TYPE

I

DRAWING NAME

11SM144

REV

8

SCALE

-

WEIGHT .006 LB MAX

SHEET 1 OF 1