

MATERIALS AND FINISHES

BODY, JAMNUT: BRASS
PLATED: NICKEL





CENTER CONTACT: BeCu
PLATED: GOLD

INTERMEDIATE CONTACT: BRASS
PLATED: GOLD

LOCKWASHER: PHOSPHOR BRONZE
PLATED: NICKEL

INSULATOR: TEFLON

GROUNDING LUGS: BRASS
PLATED: NICKEL



RECOMMENDED PANEL
CUTOUT

MIL-STD-348A, FIG 201-2	INTERFACE SPECIFICATION
SPECIFICATION	DESCRIPTION

73175-0001	73175-0000, ONE PER BAG
73175-0000	BULK
PART NO.	PACKAGING

CHG: 27.43 REF WAS 27.43±.30 A1	EC NO: URF2008-0188 2007/10/04 DRAWN: JWIENER CHKD: JFLAHERTY 2007/10/04 APPR: JWIENER 2007/10/04	DESCRIPTION NEW	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	TITLE TRIAX JACK, BLKHD.3 LUG WITH SOLDER POT TRIAX-JC MOLEX MOLEX INCORPORATED SD-73175-000 1 OF 1
				mm	INCH	DRAWN BY EDC	DATE 1999/02/08				
				4 PLACES ± --- ± ---	CHECKED BY DHG	DATE 1999/02/08					
				3 PLACES ± --- ± ---	APPROVED BY GMH	DATE 1999/02/08					
				2 PLACES ± --- ± ---	MATERIAL NO. SEE TABLE		DOCUMENT NO.				
1 PLACE ± --- ± ---		ANGULAR ± 2 °									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			