








		0.0000 [.00000]	26.42 [1.040]	31.17 [1.227]	25	26	2-111626-7
		1.0000 [.03937]	24.41 [.961]	29.18 [1.149]	23	24	2-111626-6
		1.0000 [.03937]	16.41 [.646]	21.18 [.834]	15	16	2-111626-5
		1.0000 [.03937]	8.41 [.331]	13.18 [.519]	7	8	2-111626-4
		0.0000 [.00000]	50.39 [1.984]	55.17 [2.172]	49	50	2-111626-3
		1.0000 [.03937]	44.40 [1.748]	49.17 [1.936]	43	44	2-111626-2
		1.0000 [.03937]	40.41 [1.591]	45.19 [1.779]	39	40	2-111626-1
		0.0000 [.00000]	34.42 [1.355]	39.17 [1.542]	33	34	2-111626-0
		1.0000 [.03937]	20.40 [.803]	25.17 [.991]	19	20	1-111626-9
		0.0000 [.00000]	14.40 [.567]	19.18 [.755]	13	14	1-111626-8
		0.0000 [.00000]	10.41 [.410]	15.16 [.597]	9	10	1-111626-7
OBSOLETE		1.0000 [.03937]	8.41 [.331]	13.18 [.519]	7	8	1-111626-6
OBSOLETE		0.0000 [.00000]	22.40 [.882]	27.18 [1.070]	21	22	1-111626-5
OBSOLETE		1.0000 [.03937]	68.40 [2.693]	73.18 [2.881]	67	68	1-111626-4
OBSOLETE		1.0000 [.03937]	64.41 [2.536]	69.16 [2.723]	63	64	1-111626-3
OBSOLETE		1.0000 [.03937]	60.40 [2.378]	65.18 [2.566]	59	60	1-111626-2
OBSOLETE		0.0000 [.00000]	50.39 [1.984]	55.17 [2.172]	49	50	1-111626-1
		1.0000 [.03937]	44.40 [1.748]	49.17 [1.936]	43	44	1-111626-0
OBSOLETE		1.0000 [.03937]	40.41 [1.591]	45.19 [1.779]	39	40	111626-9
OBSOLETE		0.0000 [.00000]	34.42 [1.355]	39.17 [1.542]	33	34	111626-8
OBSOLETE		0.0000 [.00000]	30.40 [1.197]	35.18 [1.385]	29	30	111626-7
OBSOLETE		0.0000 [.00000]	26.42 [1.040]	31.17 [1.227]	25	26	111626-6
OBSOLETE		1.0000 [.03937]	24.41 [.961]	29.18 [1.149]	23	24	111626-5
OBSOLETE		1.0000 [.03937]	20.40 [.803]	25.17 [.991]	19	20	111626-4
OBSOLETE		1.0000 [.03937]	16.41 [.646]	21.18 [.834]	15	16	111626-3
OBSOLETE		0.0000 [.00000]	14.40 [.567]	19.18 [.755]	13	14	111626-2
OBSOLETE		0.0000 [.00000]	10.41 [.410]	15.16 [.597]	9	10	111626-1
	CONTACT FINISH	D	C	B	A	NO OF POSN	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02-24-92 CHK C. OBERMAN J. McCLENTON 3-9-92		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.08 [.003] 3 PLC ± — 4 PLC ± — ANGLES ± ± —		NAME RECEPTACLE ASSY, 2mm CL, AMP-LATCH —	
		PRODUCT SPEC — APPLICATION SPEC —		SIZE CAGE CODE DRAWING NO A1 00779 C-111626	
MATERIAL 		FINISH 		RESTRICTED TO —	
		WEIGHT —		SCALE 10:1 SHEET 1 OF 1 REV M	
		CUSTOMER DRAWING			