

10		9	8		
ITEM	MOLEX P/N	DESCRIPTION		QTY	UOM
A,B	5051510200	2.0W/B REC HSG 2CKT		2	PC
C	5051520200	2.0W/B RETAINER 2ckt		2	PC
D	5054878000	2.0W/B CRIMP TERM AU PLATING		4	PC
PL	-	PAPER PRINTED PAPER WHITE (S100X150YAJ)		1	PC

		2		1
FROM	TO	WIRE SIZE	WIRE TYPE	COLOR
A-1	B-1	0.22 SQMM	ENDURA	BLACK
A-2	B-2	0.22 SQMM	ENDURA	BLACK

TABLE 1		
LABEL ID	LABEL CONTENT	REMARK
PL	MOLEX PN MOLEX BATCH WK/YR	LABEL TEXT MUST BE 2MM MAX IN HEIGHT WITH ARIAL FONT AND WRAPPED IN FLAG TYPE ON A SINGLE WIRE.




TABLE				
FG PART #	L1	TITLE		
2284252022	150±5	Dura-Clik TPA R-R	2Ckt	150MM disc Au
2284252024	500±5	Dura-Clik TPA R-R	2Ckt	500MM disc Au

NOTE:

1. CONNECTOR VIEW/CIRCUIT NOS SHOWN FROM THE MATING SIDE OF THE CONNECTOR, CONNECTOR VIEW IS SHOWN ONLY FOR REFERENCE. .
2. THE PRODUCT HAS TO MEET PERFORMANCE SPECIFICATION AS PER ES-36586-004.

TESTING REQUIREMENT		
TEST NAME/COMPONENT NAME	TEST PARAMETER	REQUIREMENT
Continuity/Short/Open	AS PER PIN OUT TABLE	100%

A1	FG DESCRIPTION UPDATED	ER	18/02/2025
A	INITIAL RELEASE	804956	21/11/2024
REVISION	CHANGE NOTE	EC NO	DATE
REVISION HISTORY			

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
FUNCTIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex							
		mm		NTS												
		GENERAL TOLERANCES (UNLESS SPECIFIED)			EC NO: 813242 DRWN: BHARAB52025/02/18 CHK'D: NAVEEB62025/02/19 APPR: RPAI012025/02/25											
ANGULAR TOL ± °																
4 PLACES		±														
3 PLACES		±														
2 PLACES		±														
DIVISIONAL SYMBOLS		1 PLACE		±		INITIAL REVISION: DRWN: CHIDAG12024/10/11 APPR: RPAI012024/11/22			DOCUMENT NUMBER 2284252022		DOC TYPE PSD		DOC PART 000		REVISION A1	
		0 PLACES		±												
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION												

DOCUMENT STATUS	P1	RELEASE DATE	2025/02/25 19:42:00
-----------------	----	--------------	---------------------