LinkSwitch-XT Family Energy Efficient, Lower Power Off-Line Switcher IC



NOVEMBER 2005



Typical Applications:

- Chargers/adapters for cell/cordless phones, PDAs, digital cameras, MP3/portable audio players and shavers
- · Supplies for appliances, industrial systems, and metering

PRODUCT HIGHLIGHTS

- Ideal for power supplies with tight output requirements
- Self-biased supply saves transformer auxiliary winding and associated bias supply components
- Fully integrated auto-restart for short circuit and open loop protection

FEATURES & BENEFITS

FEATURES SUPERIOR TO LINEAR/RCC

- Accurate hysteretic thermal shutdown protection automatic recovery improves field reliability
- Universal input range allows worldwide operation
- Simple ON/OFF control, no loop compensation needed
- Eliminates bias winding simpler, lower cost transformer
- Very low component count higher reliability and single side printed circuit board
- Auto-restart reduces delivered power by 95% during short circuit and open loop fault conditions
- High bandwidth provides fast turn on with no overshoot and excellent transient load response

Typical Adapter Applications



a) Clampless™ flyback converter with LNK362



b) Flyback converter	with	LNK363/4
----------------------	------	----------

OUTPUT POWER TABLE				
	230 VAC ±15%		85-265 VAC	
PRODUCT	Adapter	Open Frame	Adapter	Open Frame
LNK362P or G	2.8 W	2.8 W	2.6 W	2.6 W
LNK363P or G	5 W	7.5 W	3.7 W	4.7 W
LNK364P or G	5.5 W	9 W	4 W	6 W

See Data Sheet for Additional Notes and Conditions.

P = DIP-8



G = SMD-8

EcoSmart[®] - Extremely Energy Efficient

- Easily meets all global energy efficiency regulations with no added components
- No-load consumption <300 mW without bias winding at 265 VAC input (<50 mW with bias winding)
- ON/OFF control provides constant efficiency to very light loads – ideal for mandatory CEC regulations





LinkSwitch-XT Family Design Tools

LinkSwitch-XT Product & Design Collateral*			
Data Sheet	LNK362-364	LinkSwitch-XT Family Data Sheet	
Application Note	AN-40	LinkSwitch-XT Design Guide	
Engineering Report	EPR-89	Application: 2 W Adapter Using <i>LinkSwitch-XT</i> (<i>LNK362P</i>) (85-265 VAC Input, 6.2 V 330 mA Output)	
Design Idea	DI-89	Application: 2 W Adapter Using <i>LinkSwitch-XT</i> (<i>LNK362P</i>) (85-265 VAC Input, 6.2 V 330 mA Output)	

* Downloadable from *www.powerint.com*



DAK-89: 2 W, 6.2 V AC-DC Adapter

DAKs include a reference design power supply, sample devices, unpopulated pcb, data sheet, comprehensive engineering report & other related documentation.

Power Supply Design Software

With **PI Expert**[™] **Suite**, you're only three easy steps away from determining the key components in your next switching power supply and transformer design. It's fast & easy...and best of all, **FREE!**





EAST APPLICATION CUSTOMER TECHNICAL SUPPORT

Find relevant design information FAST!

PI FACTS identifies & displays the product information & reference designs that match your application specs. Try it now at:

www.powerint.com/facts



Design Idea DI-89

LinkSwitch-*XT* Low Cost 2 W CV Power Adapter



Application	Device	Power Output	Input Voltage	Output Voltage	Topology
Adapter	LNK362P	2 W	85-265 VAC	6.2 V	Flyback

Design Highlights

- Low-cost, low parts-count CV solution: 20 components
- Proprietary IC design and winding techniques enable a *Clampless*[™] drain-node
- ± 5% over-temperature threshold with hysteretic recovery – keeps PCB temperatures below safety limits
- Auto-restart: output short circuit and open loop protection
- IC creepage > 3.2 mm: no arcing in humid environments
- · Easily meets all EPS energy efficiency standards
- Meets CISPR-22 Class B EMI with sufficient margin

Operation

This *LinkSwitch-XT* based flyback converter (Figure 1) provides 2 W of tightly regulated constant voltage (CV) output power, while meeting the active-mode efficiency and no-load power consumption requirements of all harmonized energy efficiency (EPA, CEC) standards (see Figure 2 and Figure 3).

Diodes D1- D4 rectify the AC input. The resulting DC is filtered

by bulk storage capacitors C1 and C2. Components L1, L2, C1 and C2 form a conducted EMI noise filter. Resistor R1 dampens the ringing of the filter. Switching frequency jitter and PI's *E-Shield*TM transformer construction technology enable this design to meet EN55022 Class-B conducted EMI with good margin (see Figure 4). Y capacitor C4 (optional) can improve the unit-to-unit repeatability of EMI scans.

This supply also takes advantage of PI's *Clampless* transformer techniques, which uses T1's primary winding capacitance to clamp the voltage spike that its leakage inductance causes, each time the MOSFET in U1 turns off. Therefore, this converter has no primary clamp components connected to the drain-node.

From no-load until maximum output power (2 W) is delivered, the LNK362P (U1) regulates the output voltage by skipping switching cycles, based on the current delivered into the feedback (FB) pin. If the output is over loaded and no feedback (< 49 μ A) is received within a 40 ms period, U1 goes into autorestart mode. In auto-restart, MOSFET switching is enabled for about 40 ms approximately every 800 ms if no feedback is received within the 40 ms window of enabled switching.



Figure 1. LNK362 Based 6.2 V, 322 mA, 2 W, Low-Cost, Flyback CV Output Power Adapter.

DI-89

Key Design Points

- The PI Xls spreadsheet calculates all of the parameters required to specify and build transformer T1.
- The power transformer must have a two layer primary winding to ensure that its intra-winding capacitance is sufficient for Clampless operation.
- The reflected output voltage (V_{OR}) of this design was kept < 90 V (74 V) for Clampless operation.
- Since this supply has a Clampless drain node, it must be verified that the maximum drain voltage does not exceed 650 V when the flyback voltage spike occurs.
- The primary current ripple-to-peak ratio (K_p) factor should be > 1 (ensures discontinuous conduction mode operation) to minimize conducted EMI.
- The maximum operating flux density (B_M) was kept < 1500 Gauss to eliminate audible.



Figure 3. Harmonized (EPA, CEC) Active-Mode Efficiency vs. Output Power (25, 50, 75 & 100%).



Figure 2. No-Load Input Power Consumption vs. Input Voltage.



Figure 4. Conducted EMI Scan to EN55022B Limits: Full-Load, 115 VAC, 60 Hz Input, with Artificial Hand.

For the latest updates, visit www.powerint.com

Power Integrations reserves the right to make changes to its products at any time to improve reliability or manufacturability. Power Integrations does not assume any liability arising from the use of any device or circuit described herein. POWER INTEGRATIONS MÄKES NO WARRÄNTY HEREIN AND SPECIFICALLY DISCLAIMS ALL WARRANTIES INCLUDING, WITHOUT LIMITATIONS, THE IMPLIED WARRÄNTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF THIRD PARTY RIGHTS. The products and applications illustrated herein (transformer construction and circuits external to the products) may be covered by one or more U.S. and foreign patents or potentially by pending U.S. and foreign patent applications assigned to Power Integrations. A complete list of Power Integrations' patents may be found at www.powerint.com. Power Integrations grants its customers a license under certain patent rights as set forth at http://www.powerint.com/ip.htm.

The PI logo, TOPSwitch, TinySwitch, LinkSwitch, DPA-Switch, EcoSmart, Clampless, E-Shield, Filterfuse, PI Expert and PI FACTS are trademarks of Power Integrations, Inc. Other trademarks are property of their respective companies. Copyright 2005, Power Integrations, Inc.

POWER INTEGRATIONS WORLDWIDE SALES SUPPORT LOCATIONS

CATIONS HOTLINE +1 408-414-9660 +1 408-414-9760	CHINA (SHANGHAI) Shanghai, China Phone: +86-21-6215-5548 E-mail: chinasales@powerint.com
OMER SERVICE +1 408-414-9665 +1 408-414-9765	CHINA (SHENZHEN) Shenzhen, China Phone: +86-755-8379-3243 E-mail: chinasales@powerint.com

WORLD HEADQUARTERS San Jose, CA, USA +1 408-414-9200 Phone: E-mail: usasales@powerint.com

APPLI

Phone:

CUST

Phone:

Fax:

Fax:

GERMANY Munich, Germany +49-89-5527-3910 Phone E-mail: eurosales@powerint.com

INDIA Bangalore, India +91-80-5113-8020 Phone: E-mail: indiasales@powerint.com

ITALY Milano, Italy +39-028-928-6000 Phone: E-mail: eurosales@powerint.com

JAPAN Kanagawa, Japan +81-45-471-1021 Phone: E-mail: japansales@powerint.com KOREA Seoul, Korea +82-2-2016-6610 Phone: E-mail: koreasales@powerint.com

+65-6358-2160

E-mail: singaporesales@powerint.com

+886-2-2659-4570

E-mail: taiwansales@powerint.com

SINGAPORE

Singapore

TAIWAN

Phone:

Taipei. Taiwan

Phone:

EUROPE HQ

Farnham, Surrey, United Kingdom +44 (0) 1252-730-140 Phone: E-mail: eurosales@powerint.com

For a complete list of our Worldwide Sales Representatives & Distributors visit our Web site: www.powerint.com