

Quam

SYSTEM VP1/SYSTEM VP2

Surface mounted

Vandal-proof Speaker Systems



System 1 VP

Features

- All-steel construction
- Outdoor treated speaker
- Integral security grill
- Durable finish
- In stock for immediate shipment



System 2 VP

The System VP1 and System VP2 are surface mounted speaker systems that are designed for areas prone to vandalism. Typical applications include public areas, parking garages, security systems and correctional facilities. To prevent damage of the speaker, a special 22 gauge steel security screen is

mounted between the speaker and the vandal-resistant grill. Tamper-resistant mounting hardware is included. The moisture-resistant speaker and enclosure allow these units to be mounted outdoors. Both systems are finished in durable baked white powder epoxy.

SPECIFICATIONS

SPEAKER

TYPE
FREQ. RANGE
POWER RATING
SENSITIVITY
MAGNET SIZE
VOICE COIL
CONE TYPE

TRANSFORMER

POWER RATING
PRIMARY VOLT
PRIMARY TAPS
TERMINATIONS

GRILL

FINISH
MATERIAL

ENCLOSURE

MATERIAL
FINISH
MOUNTING HOLES
FACE
NET WEIGHT

8C10PAOT

8" P.C.
80-8000Hz
15 WATTS
96 dB SPL (1 WATT 1 METER)
10 OZ.
8 OHM
IMPREGNATED CLOTH

TBLU

5 WATTS
25/70
5/16, 5/8, 1-1/4, 2-1/2, AND 5 WATTS
(9) 6" LEADS COLOR CODED

BS8VP

BAKED WHITE POWDER EPOXY
14 GAUGE STEEL

SE1WVP (SYSTEMVP1),

SE2WVP (SYSTEM VP2)

.060" COLD ROLLED STEEL
BAKED WHITE POWDER EPOXY
10" SQUARE
FLAT (SYSTEM VP1), TAPERED (SYSTEM VP2)
11 LBS.

Architects & Engineers Specifications

The surface speaker system shall be a Quam (System VP1) (System VP2) or approved equal. The speaker shall be a Quam Model 8C10PAOT with integral TBLU transformer pre-mounted. The transformer shall have taps for either 25 or 70 volt lines. The power taps shall be 5/16, 5/8, 1-1/4, 2-1/2, and 5 watts. The speaker frequency response shall be 80-8KHz. The speaker sensitivity shall be 96dB minimum at a distance of one meter with one watt applied. The speaker shall employ a ten ounce ceramic magnet. Flex density shall be 9,500 Gauss minimum. The speaker shall

be factory assembled to a Quam Model BS8VP baffle.

The baffle shall be zinc treated 14 gauge steel finished in baked white powder epoxy. The system shall utilize an interior steel security screen between the speaker and baffle opening. System VP1 shall measure 11.65" high, 11.65" wide and 4" deep. System VP2 shall measure 11.65" high, 11.65" wide and shall have a sloped depth of 5.25" at the top down to 2.75" depth at the bottom. The enclosure shall be .060" zinc treated steel and shall be finished in white baked powder epoxy.



Quam

Quam-Nichols Company

234 East Marquette Road • Chicago, IL 60637
(773) 488-5800 • FAX (773) 488-6944



Member



TS-55