










Section A-A




Scale 6



LF Contacts number	Distance in mm between axes		Length in mm	LF Contacts reference mark number			
XXX	A	B	C	D	E	F	G
004	1,27	8,27	12,87	I	2	3	4
006	2,54	9,54	14,14	I	3	4	6
008	3,81	10,81	15,41	I	4	5	8
010	5,08	12,08	16,68	I	5	6	10
012	6,35	13,35	17,95	I	6	7	12
014	7,62	14,62	19,22	I	7	8	14
016	8,89	15,89	20,49	I	8	9	16
018	10,16	17,16	21,76	I	9	10	18
020	11,43	18,43	23,03	I	10	11	20
022	12,7	19,7	24,3	I	11	12	22
024	13,97	20,97	25,57	I	12	13	24
026	15,24	22,24	26,84	I	13	14	26
028	16,51	23,51	28,11	I	14	15	28
030	17,78	24,78	29,38	I	15	16	30
032	19,05	26,05	30,65	I	16	17	32
034	20,32	27,32	31,92	I	17	18	34
036	21,59	28,59	33,19	I	18	19	36
038	22,86	29,86	34,46	I	19	20	38
040	24,13	31,13	35,73	I	20	21	40
042	25,4	32,4	37	I	21	22	42
044	26,67	33,67	38,27	I	22	23	44
046	27,94	34,94	39,54	I	23	24	46
048	29,21	36,21	40,81	I	24	25	48
050	30,48	37,48	42,08	I	25	26	50
052	31,75	38,75	43,35	I	26	27	52
054	33,02	40,02	44,62	I	27	28	54
056	34,29	41,29	45,89	I	28	29	56
058	35,56	42,56	47,16	I	29	30	58
060	36,83	43,83	48,43	I	30	31	60

Notes:

1. "XXX" to be replaced by the number of LF contacts.
2. In commercial designation X to be replaced by the type of crimp contacts, A or B or G
3. Connector delivered with fittings assembled.
4. General tolerance $\pm 0,2$



M I C R O H D A S
M a l e c o n n e c t o r
M H D A S 2 M X X X X E 0 2

DRAWN BY : S Satpute		UPDATED BY : A Samanta		LAST APPROVED BY : R Courtin	
ALL DIMENSIONS ARE IN MM		AMPHENOL SOCAPEX		ORIGINAL DRAWING DATE : 23/05/2022	
				CONFIGURATION DATA ARE AVAILABLE IN PDF	
SCALE : 6		B.P. 29 74311 THYEZ CEDEX		REV : D PAGE : 1/	
		169-PLC-1726-00			