




IN THE CONSTANT PURPOSE OF IMPROVING ITS PRODUCTS, Amphenol Socapex reserves the right to modify any dimension or characteristics.
FM.NPD.0037.THYZE.PUNE rev C




Final position (After fastening)

PCB Layout




Notes:


- "XXX" to be replaced by the number of LF contacts.
- Connector delivered with fittings not assembled, coupling torque: 0,2 Nm for M2.5 & 0.16 Nm for M1.6
- General tolerance $\pm 0,2$



Section A-A



Initial position (Before fastening)



MICRO HDAS
Female connector
MHDAS 2 F XXX YD E03

LF Contacts number	Distance in mm between axes		Length in mm	LF Contacts reference mark number			
	A	B		D	E	F	G
004	1,27	8,27	12,87	I	2	3	4
006	2,54	9,54	14,14	I	3	4	6
008	3,81	10,81	15,41	I	4	5	8
010	5,08	12,08	16,68	I	5	6	10
012	6,35	13,35	17,95	I	6	7	12
014	7,62	14,62	19,22	I	7	8	14
016	8,89	15,89	20,49	I	8	9	16
018	10,16	17,16	21,76	I	9	10	18
020	11,43	18,43	23,03	I	10	11	20
022	12,7	19,7	24,3	I	11	12	22
024	13,97	20,97	25,57	I	12	13	24
026	15,24	22,24	26,84	I	13	14	26
028	16,51	23,51	28,11	I	14	15	28
030	17,78	24,78	29,38	I	15	16	30
032	19,05	26,05	30,65	I	16	17	32
034	20,32	27,32	31,92	I	17	18	34
036	21,59	28,59	33,19	I	18	19	36
038	22,86	29,86	34,46	I	19	20	38
040	24,13	31,13	35,73	I	20	21	40
042	25,4	32,4	37	I	21	22	42
044	26,67	33,67	38,27	I	22	23	44
046	27,94	34,94	39,54	I	23	24	46
048	29,21	36,21	40,81	I	24	25	48
050	30,48	37,48	42,08	I	25	26	50
052	31,75	38,75	43,35	I	26	27	52
054	33,02	40,02	44,62	I	27	28	54
056	34,29	41,29	45,89	I	28	29	56
058	35,56	42,56	47,16	I	29	30	58
060	36,83	43,83	48,43	I	30	31	60

DRAWN BY: A Samanta		UPDATED BY: A Samanta		LAST APPROVED BY: M Gervais	
ALL DIMENSIONS ARE IN MM		SCALE: 7		ORIGINAL DRAWING DATE: 11/03/2023	
AMPHENOL SOCAPEX		B.P. 29 74311 THYZE CEDEX		CONFIGURATION DATA ARE AVAILABLE IN PDM	
				REV: D	
				PAGE: 1/1	
				169-PLC-1767-00	

EXPORT CONTROL CLASSIFICATION NOT CONTROLLED/EAR99

Information contained in this document is not subject to Export Control Regulations of the European Union, USA or other countries. Each recipient of this document is responsible for ensuring that transfer or use of any information contained in this document complies with all relevant Export Control regulations and EAR99 regulations.