






TABLE 1	
AHSP P/N	LENGTH "A"
NDAAXF-0001	1000 ±20
NDAAXF-0002	500 ±20
NDAAXF-0003	1500 ±40
NDAAXF-0004	2000 ±40


REVISIONS		ZONE	REV.	ECN NUMBER	DESCRIPTION	BY	DATE	APPROVED
C				ALOZ-19082802	UPDATED NOTE #6 ADDED CE STAMP	HCL-SH	09/05/2019	ERDEM.M
D				JCHN-19122701	DELETED ITEM #4 IN TABLE 2, UPDATED FRONT VIEW.	HCL-PB	01/06/2020	J.CHEN
E				DDYR-23051501	ADDED NEW P/N -0004 TO TABLE 1.	QJ.DAI	05/22/2023	MARK.H

NOTE: ONLY THREE MOST RECENT RELEASED REVISIONS DISPLAYED



RADIUS FROM END OF DIECAST


TABLE 2	
ITEM No.	DESCRIPTION
1	30 AWG, 8-PR, PVC BLACK, UL AWM STYLE 20276, 80°C, VW1
2	PLUG, QSFP+, REFERENCE SFF-8661
3	LABEL, WRAPPED - AHSP P/N, REV, DATE CODE, LENGTH, CoO & SERIAL NUMBER
5	LANYARD - PANTONE 347C (GREEN)
6	LABEL, CONNECTOR - AHSP P/N, REV, DATE CODE LENGTH, CoO & SERIAL NUMBER



NOTE: DC BLOCKING CAP VALUE IS 0.1 μF
EPROM CONNECTED TO VCCTX

- UL LABEL MUST BE ON THE SHIPPING CARTON PER SUBJECT 764 OF THE UL COMPONENT WIRING HARNESS (ZPFW2) FILE #E86140. CSA LABEL MUST BE ON SHIPPING CARTON.
- PACKAGE COMPLETED ASSY IN AN APPROPRIATELY SIZED ESD BAG.
- EPROM CONTENT SHALL BE COMPLIANT WITH SFF-8636 SPECIFICATIONS. EPROM REVISION IS EQUAL TO AHSP PART NUMBER REVISION.
- ASSEMBLIES LESS THAN ONE METER REQUIRE ONLY ONE LABEL PLACED ON P1 END.
- CABLE ASSEMBLIES MUST MEET SHIELDING EFFECTIVENESS REQUIREMENTS OF 35dB FROM 1-10GHz AND 30dB FROM 10-18GHz.
- COMPLIANT TO EU DIRECTIVE 2011/65/EU - RoHS2.
- ASSEMBLIES SHALL BE COMPLIANT TO IEEE 802.3cd 200GBASE-CR4 SPECIFICATION.
- THIS DRAWING IS RESERVED FOR AMPHENOL STANDARD PRODUCT.

NOTES: UNLESS OTHERWISE SPECIFIED



CODE IDENT 31413

TOLERANCES		DWN	9/6/2017	Amphenol AHSF A Division of Amphenol Corporation 200 Innovative Way, Suite 201, Nashua, N.H. 03062 (603) 879-3505		
0.0	± 0.25	DC				
0.00	± 0.08	CHK	9/6/2017			
		DJD				
0.000	± —	APVD	9/6/2017	TITLE CABLE ASSEMBLY, QSFP/QSFP, PSV, 100Ω, 200 GbE, 30 AWG EXD		
ANGLES	± 1.0°	EM				
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MM						
CUSTOMER USE DRAWING				PART NO.	REV	
				SEE TABLE 1		N/A
				DRAWING NO.	REV	
				C—NDAAXF—0099		E
SIZE		D	SCALE	1:1	SHEET 1 OF 1	

CUSTOMER USE
DRAWING