


3M™ HIGH FLEX LIFE CABLE, 3319 SERIES
.050" 28 AWG STRANDED, PVC



ORDERING INFORMATION

X 3319 / XX XX
BLANK = STANDARD
C = CANADIAN CERTIFIED VERSION
BLANK = STANDARD
SF = SPLICE FREE
NUMBER OF CONDUCTORS (SEE TABLE 1)

NOTE:
AVAILABLE IN STANDARD LENGTHS OF 100 FT OR 300 FT ROLLS,
PLEASE SPECIFY WHEN ORDERING.
CONTACT 3M FOR AVAILABILITY OF ADDITIONAL CONDUCTOR COUNTS
AND/OR CUSTOM ROLL LENGTHS.

TABLE 1
DIMENSION CHART

NUMBER OF CONDUCTORS	3M PART NUMBER	DIMENSION "A"	DIMENSION "B"
06	3319/06	.300±.010 [7.62]	.250±.007 [6.35]
08	3319/08	.400±.010 [10.16]	.350±.007 [8.89]
09	3319/09	.450±.010 [11.43]	.400±.007 [10.18]
10	3319/10	.500±.010 [12.70]	.450±.007 [11.43]
14	3319/14	.700±.010 [17.78]	.650±.007 [16.51]
15	3319/15	.750±.010 [19.05]	.700±.007 [17.78]
16	3319/16	.800±.015 [20.32]	.750±.011 [19.05]
20	3319/20	1.000±.015 [25.40]	.950±.011 [24.13]
24	3319/24	1.200±.015 [30.48]	1.150±.011 [29.21]
25	3319/25	1.250±.015 [31.75]	1.200±.011 [30.48]
26	3319/26	1.300±.015 [33.02]	1.250±.011 [31.75]
30	3319/30	1.500±.020 [38.10]	1.450±.015 [36.83]
34	3319/34	1.700±.020 [43.18]	1.650±.015 [41.91]
36	3319/36	1.800±.020 [45.72]	1.750±.015 [44.45]
37	3319/37	1.850±.020 [46.99]	1.800±.015 [45.72]
40	3319/40	2.000±.020 [50.80]	1.950±.015 [49.53]
50	3319/50	2.500±.020 [63.50]	2.450±.015 [62.23]
60	3319/60	3.000±.020 [76.20]	2.950±.015 [74.93]
64	3319/64	3.200±.020 [81.28]	3.150±.015 [80.01]

"PRINTING ILLUSTRATION"



AWM 2651 105°C 300V VW1 3M NU



AWM IA 105°C 300V FT1 EU <50V



UL FILE NO: E42769
UL STYLE NO: 2651

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

- * FLEX LIFE OF 100 MILLION CYCLES AT 1-3/4 INCH DIAMETER.
- * 19 STRANDS OF HIGH STRENGTH COPPER ALLOY PROVIDE THE LONGEST FLEX LIFE AVAILABLE FOR DYNAMIC APPLICATIONS.
- * 28 AWG WIRE ON .050 INCH WIRE SPACING PERMITS MASS TERMINATION TO A BOARD LINE OF IDC CONNECTORS.
- * ZIPPABLE FOR BRANCHING OR DISCRETE TERMINATION.

- REGULATORY INFORMATION:
VISIT 3M.com/regs
- IN THE EVENT OF CONFLICT BETWEEN THIS DATA AND THAT CONTAINED IN THE PRODUCT SPECIFICATION, THE PRODUCT SPECIFICATION TAKES PRECEDENT.
- RED MARKING ON ONE EDGE OF CABLE DESIGNATES WIRE #1.

2 PHYSICAL :

INSULATION: POLYVINYL CHLORIDE (PVC)
MATERIAL: COLOR: BLACK

MARKING: NONE
STANDARD: SEE "PRINTING ILLUSTRATION" BELOW
CANADIAN: 28 AWG, 19 X 40 AWG [19 X Ø0.079] SILVER PLATED
CONDUCTORS: STRANDED COPPER ALLOY (89% CONDUCTIVITY)

2 TABLE 2
ELECTRICAL CHARACTERISTICS

VOLTAGE RATING	USA: 300V, CANADA: 300V, EU: <50V	
INSULATION RESISTANCE	PRIMARY CABLE >1 X 10 ¹⁰ Ω/10 FT [3 m]	
	UNBALANCED	BALANCED
CHARACTERISTIC IMPEDANCE	103 Ω	171 Ω
CAPACITANCE	13.6 pF/ft [44.62 pF/m]	7.9 pF/ft [25.91 pF/m]
INDUCTANCE	0.14 μH/ft [0.47 μH/m]	0.23 μH/ft [0.76 μH/m]
PROPAGATION DELAY	1.40 ns/ft [4.59 ns/m]	1.35 ns/ft [4.43 ns/m]
VELOCITY OF PROPAGATION	73%	75%

NOTE: UNBALANCED IS MEASURED BETWEEN GROUND-SIGNAL-GROUND CONDUCTORS.
BALANCED IS MEASURED BETWEEN SIGNAL CONDUCTORS WITHIN A PAIR.

2 ENVIRONMENTAL :

TEMPERATURE RATING: -20°C TO +105°C

FLAMMABILITY RATING: USA; VW1 CANADA; FT1

DIMENSIONS: INCHES [MM]
[MM] IS FOR REF. ONLY

DESIGN REFERENCE	NEXT ASSEMBLY	REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
XXXXXX	XXXXXX	ECO	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
DIVISION	DIVISION CODE	DRFT	CHKD	DATE	DATE	DATE
DO NOT SCALE DRAWING	SCALE	DATE	DATE	DATE	DATE	DATE
THIRD ANGLE PROJECTION	INTERPRET PER ASME Y14.5 - 2018	DATE	DATE	DATE	DATE	DATE
MAX. SURFACE ROUGHNESS	ALL SURFACES	DATE	DATE	DATE	DATE	DATE
MARKED ONLY	ANGLES	DATE	DATE	DATE	DATE	DATE
TOLERANCES EXCEPT AS NOTED		3M Center St. Paul, MN 55144				
INCHES .00 ± .01 .000 ± .005 .0000 ± .0005		© 3M COPYRIGHT 2024. This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.				
MILLIMETERS 0 ± .00 ± .000 ± .000		TITLE MEDIUM FLEX LIFE FLAT CABLE, .050", 28 AWG, 3319				
CAGE NUMBER		SIZE	DRAWING NO.	REV.		
D		D	78-5100-0059-5	D		
MODEL		3319	LISTS	YES	NO	SHT 1 OF 2

3M™ HIGH FLEX LIFE CABLE, 3319 SERIES

Regulatory: For regulatory information about this product, visit 3M.com/regs or contact your 3M representative.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: For industrial use only. Not intended, labeled or packaged for consumer sale or use.

3M Company
Electronics Materials Solutions Division
13011 McCallen Pass, Bldg. C
Austin, TX 78753-5380
1-800-225-5373
www.3M.com/interconnect

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

		D	I 18693	OCT 08, 2024		JNC	JG
		C	64249	ADD CABLE 3319/08		JNC	JJR
		B	23269	JUN 29, 2023 REVISED NOTES AND REDRAWN		JNC	JJR
		A	AT2268	APR 22, 2009 REVISE NOTES		RED	ARM
		A	AT2268	APR 23, 2007 UPDATE TO NEW FORMAT		RED	ARM
DESIGN REFERENCE		NEXT ASSEMBLY					
ACCESS CODES							
DIVISION		DIVISION CODE		DATE		DATE	
DO NOT SCALE DRAWING		EMSD		JUN 29, 2023		JUN 29, 2023	
SCALE		TOLERANCES EXCEPT AS NOTED		APPROVAL		DATE	
THIRD ANGLE PROJECTION		INCHES		F. RODRIGUEZ		JUN 29, 2023	
INTERPRET PER ASME Y14.5 - 2018		MILLIMETERS		3M Center St. Paul, MN 55144		© 3M COPYRIGHT 2024 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.	
MAX SURFACE ROUGHNESS		ANGLES		TITLE		REV.	
ALL SURFACES		0 ±		MEDIUM FLEX LIFE FLAT		CAGE NUMBER	
MARKED ONLY		0.00 ±		CABLE, .050" , 28 AWG,		SIZE	
✓		0.000 ±		3319		DRAWING NO.	
		0.00 ±		D		D	
		0.000 ±		578-5100-0059-5		D	
		0.00 ±		MODEL		DET.	
		0.000 ±		3319		LISTS	
		0.00 ±				YES	
		0.000 ±				YES	
		0.00 ±				NO	
		0.000 ±				SHT 2 OF 2	