


**W** WELDY  
Hot Air Tools

Hot air tools for  
do-it-yourself



*fun at work*

**WELDY PIC**

**WELDY PRO**

**WELDY PLUS**




Weldy  
program





# WELDY PLUS

digital hot air tool




- 1 terminal display with memory function
- 2 function programmes
- 3 temperature and airflow adjustment
- 4 Stand-by for eco-drive


- 5 tool stand
- 6 ergonomical distribution of weights
- 7 non-slip handle
- 8 main switch

## Function programmes / digital display


By operating the key on the menu, the required function program can be selected



manuel drive



shrinking



forming




welding



soldering



paint stripping



drying



# Intelligent hot air tools for do-it-yourself

## BASIC WELDY PIC



## ELECTRONIC WELDY PRO




## DIGITAL WELDY PLUS



### Technical data

Voltage	230,
Power consumption	1600 W
Temperature range	350°C or 500°C
Airflow	350 or 500 l/min
Max. static pressure	1250 Pa
Weight	500 g
On/off switch	2-step switch
Temperature adjustment	2-step
Airflow adjustment	2-step
Heating element	protected

### Accessories



### Technical data

Voltage	230,
Power consumption	1800 W
Temperature range	100°C to 550°C
Airflow	250 or 550 l/min
Max. static pressure	1300 Pa
Weight	570 g
On/off switch	2-step switch
Temperature adjustment	potentiometer, stepless temperature adjustment with scale
Airflow adjustment	2-step
Electronics	flicker-conformity
Heating element	protected


### Accessories










### Technical data

Voltage	230,
Power consumption	2000 W
Temperature range	80°C to 650°C
Airflow	200 to 550 l/min adjustable
Max. static pressure	1200 Pa
Weight	620 g
On/off switch	main switch
Temperature and airflow adjustment	terminal with menu control
Display	LCD-display
Electronics	temperature control independent of airflow and power supply, program with seven function, memory, stand-by for eco drive flicker conformity
Heating element	all ceramic, protected

### Accessories





**Intelligent Weldy hot air tools  
for all budgets**

ISO 9001

SEV, CCA zertifiziert

CE-Konform

**EcoTool**

**LEISTER**

Riedstrasse, CH-6060 Sarnen/Switzerland

Tel. +41-41-662 75 88 Fax +41-41-662 75 02

e-mail: [ecotool@ecotool.com](mailto:ecotool@ecotool.com)

[www.weldytool.com](http://www.weldytool.com)