

SHELL SIZE	REFERENCE PART NO	AIJPL PART NO	'A' +0.031 -0.016	'B' MAX CLOSED	'C' MAX	'D' MIN	'E' MAX	'F' MIN	'G' THREAD -2A	'H' THREAD -2B	'J' APPROX. (GLAND)		MAX CABLE ENTRY
											FREE	CLOSED	
10SL, 12S	MS3057-4C	A3057-4C	0.188	0.296	0.937	0.594	1.375	0.500	0.1380-32 UNC	0.6250-24 NEF	0.312	0.094	0.312
14S	MS3057-6C	A3057-6C	0.188	0.390	1.062	0.594	1.375	0.500	5-40 UNC	0.7500-20 NEF	0.438	0.250	0.438
16S, 16	MS3057-8C	A3057-8C	0.188	0.434	1.188	0.719	1.375	0.500	0.1380-32 UNC	0.8750-20 UNEF	0.531	0.312	0.515
18	MS3057-10C	A3057-10C	0.188	0.434	1.312	0.719	1.437	0.500	0.1380-32 UNC	1.0000-20 UNEF	0.625	0.375	0.614
20, 22	MS3057-12C	A3057-12C	0.250	0.596	1.562	0.844	1.437	0.500	0.1640-32 UNC	1.1875-18 UNEF	0.750	0.500	0.738
24, 28	MS3057-16C	A3057-16C	0.250	0.596	1.750	1.062	1.562	0.500	0.1640-32 UNC	1.4375-18 UNEF	0.938	0.594	0.926
32	MS3057-20C	A3057-20C	0.312	0.858	2.250	1.187	1.812	0.531	0.2500-20 UNC	1.7500-18 NS	1.250	0.938	1.200
36	MS3057-24C	A3057-24C	0.312	0.858	2.375	1.200	2.062	0.750	0.2500-20 UNC	2.0000-18 NS	1.375	0.969	1.363
40	MS3057-28C	A3057-28C	0.312	1.107	2.625	1.312	2.062	0.750	0.2500-20 UNC	2.2500-16 NS	1.625	1.138	1.611

ORDERING INFORMATION

A3057-XXC-YYY

SERIES

DASH NO

FINISH

MATERIAL



COMPONENT	MATERIAL	PLATING FINISH
BODY	ALUMINUM ALLOY	REFER FINISH (YYY)
CLAMP		ELECTROLESS NICKEL
SLEEVE		
GLAND	SILICONE RUBBER	-
SCREW	COPPER ALLOY	REFER FINISH (YYY)
WASHER		

FINISH (YYY)

NONE	CAD. PLATE OLIVE DRAB GREEN
416/ A23	ELECTROLESS NICKEL
622	CAD. FREE ZINC COBALT OD GREEN
624	CAD. FREE ZINC COBALT BLACK
726	ELECTROPHATIC BLACK

5	06/02/25
Issue No.	Rev. Date.

ALL DIM'S ARE IN INCHES



SHEET 1 OF 1		STRAIN RELIEF CABLE CLAMP ASSEMBLY TYPE A3057-XXC		Drawn by: SACHIN		Amphenol	
Scale N.T.S.		Dwg. No. C-80520/A		Date 08/08/24		Amphenol Interconnect India Pvt. Ltd.	
						PUNE-411026	