




1			2		3		4																																																																									
A	WARNING All Drawings and Specifications are and remain our Property and must be returned to us. All Specifications and Drawings are confidential and are not to be disclosed to any persons other than those to whom they are sent. Unauthorized reproduction in any form of this Drawing in part or full is prohibited.			ISSUE NO.	Eng Ref. NO.	REVISIONS	DATE	APP. BY.																																																																								
				01	---	ORIGINAL	11/01/24	SPK																																																																								
				02	3949 2946	REVISED	23/01/24	Kabon																																																																								
B																																																																																
C	<table border="1"><thead><tr><th>REF.PART CODE</th><th>AIPL PART CODE</th><th>ØC</th><th>L</th><th>ØD</th><th>ØA</th></tr></thead><tbody><tr><td>MS3420-3</td><td>A3420-3</td><td>9.50</td><td>73.02</td><td>5.33</td><td>3.30</td></tr><tr><td>MS3420-4</td><td>A3420-4</td><td>12.80</td><td>69.80</td><td>7.70</td><td>5.60</td></tr><tr><td>MS3420-6</td><td>A3420-6</td><td>15.60</td><td>66.68</td><td>10.85</td><td>7.92</td></tr><tr><td>MS3420-8</td><td>A3420-8</td><td>18.77</td><td>63.50</td><td>14.02</td><td>11.10</td></tr><tr><td>MS3420-10</td><td>A3420-10</td><td>21.95</td><td>60.33</td><td>15.62</td><td>14.27</td></tr><tr><td>MS3420-12</td><td>A3420-12</td><td>26.90</td><td>57.15</td><td>18.80</td><td>15.88</td></tr><tr><td>MS3420-16</td><td>A3420-16</td><td>33.38</td><td>53.98</td><td>23.55</td><td>19.05</td></tr><tr><td>MS3420-20</td><td>A3420-20</td><td>40.41</td><td>50.80</td><td>31.50</td><td>23.80</td></tr><tr><td>MS3420-24</td><td>A3420-24</td><td>46.79</td><td>47.62</td><td>34.67</td><td>31.75</td></tr><tr><td>MS3420-28</td><td>A3420-28</td><td>53.00</td><td>44.45</td><td>41.00</td><td>34.90</td></tr><tr><td>MS3420-40</td><td>A3420-40</td><td>72.00</td><td>38.10</td><td>60.05</td><td>47.60</td></tr></tbody></table>								REF.PART CODE	AIPL PART CODE	ØC	L	ØD	ØA	MS3420-3	A3420-3	9.50	73.02	5.33	3.30	MS3420-4	A3420-4	12.80	69.80	7.70	5.60	MS3420-6	A3420-6	15.60	66.68	10.85	7.92	MS3420-8	A3420-8	18.77	63.50	14.02	11.10	MS3420-10	A3420-10	21.95	60.33	15.62	14.27	MS3420-12	A3420-12	26.90	57.15	18.80	15.88	MS3420-16	A3420-16	33.38	53.98	23.55	19.05	MS3420-20	A3420-20	40.41	50.80	31.50	23.80	MS3420-24	A3420-24	46.79	47.62	34.67	31.75	MS3420-28	A3420-28	53.00	44.45	41.00	34.90	MS3420-40	A3420-40	72.00	38.10	60.05	47.60
REF.PART CODE	AIPL PART CODE	ØC	L	ØD	ØA																																																																											
MS3420-3	A3420-3	9.50	73.02	5.33	3.30																																																																											
MS3420-4	A3420-4	12.80	69.80	7.70	5.60																																																																											
MS3420-6	A3420-6	15.60	66.68	10.85	7.92																																																																											
MS3420-8	A3420-8	18.77	63.50	14.02	11.10																																																																											
MS3420-10	A3420-10	21.95	60.33	15.62	14.27																																																																											
MS3420-12	A3420-12	26.90	57.15	18.80	15.88																																																																											
MS3420-16	A3420-16	33.38	53.98	23.55	19.05																																																																											
MS3420-20	A3420-20	40.41	50.80	31.50	23.80																																																																											
MS3420-24	A3420-24	46.79	47.62	34.67	31.75																																																																											
MS3420-28	A3420-28	53.00	44.45	41.00	34.90																																																																											
MS3420-40	A3420-40	72.00	38.10	60.05	47.60																																																																											
D	NOTE: - LESS THAN 0.5MM RAISED PARTLINE(FLASH) IS ACCEPTABLE. - MATERIAL:NEOPRENE IN ACCORDANCE WITH AMS3208, BLACK 40 TO+100° C(-40 TO +212°F). - HARDNESS:-50±5 DUROMETER.																																																																															
E																																																																																
F				SL.NO.		DRG.NO.		FINISH																																																																								
<table border="1"><thead><tr><th>NAME</th><th>DATE</th></tr></thead><tbody><tr><td>Drawn by NANDA</td><td>11.01.24</td></tr><tr><td>Checked by P. K. N. S.</td><td>23/01/24</td></tr><tr><td>App. by Kabon</td><td>23/01/24</td></tr></tbody></table>			NAME	DATE	Drawn by NANDA	11.01.24	Checked by P. K. N. S.	23/01/24	App. by Kabon	23/01/24	Amphenol Amphenol Interconnect India Pvt. Ltd. BANGALORE - 560 100				Mat.Spec. SEE NOTE-2																																																																	
NAME	DATE																																																																															
Drawn by NANDA	11.01.24																																																																															
Checked by P. K. N. S.	23/01/24																																																																															
App. by Kabon	23/01/24																																																																															
TOLERANCES DECIMALS : ±0.10 ANGLES : ±2° Scale:- NTS			TITLE OUT LINE DWG FOR TELESCOPIC BUSH A3420-XX				 																																																																									
SURFACE AREA: N/A			Dwg. No. B76320		All Dimensions are in MM/INCHES Sheet 1 OF 1																																																																											
QF-DEV-83 REV.NO. :03																																																																																