


STEINEL®

STEINEL®

Into the Blue



STEINEL · 9051 Lyndale Avenue South · Bloomington · MN 55420
Telephone 800-852-4343 · Fax 952-888-5132 · www.steinell.net · sales@steinell.net

HB 1750

Professional Heat Blower Series

The HB 1750 is the most ergonomically advanced high output blower in its class.

21st Century technology enables STEINEL to achieve maximum airflow from a lightweight, ultra quiet tool. Superior design, materials and workmanship ensure the quality and reliability the STEINEL name guarantees.

For world-class performance...Come Into the Blue.


Introducing STEINEL Heat Blowers



Shrink wrap, packaging ...



Dry paint, wall emulsion, filler etc.



Fully adjustable quick-lock stand conveniently stores temperature keys. Tool removes easily for hand-held operation.

HB 1750

High Output

- Powerful turbine blower with air delivery rate up to 23 CFM
- Color coded keys for the right temperature every time
- Maintenance free factory sealed motor

Superior Ergonomics

- Lightweight, well balanced design
- Soft grip handle with convenient slide switch (Off / Cool / Hot)
- Ultra quiet operation

Convenient Operation

- Plug-in heating element takes only seconds to change
- Quick-lock stand is fully adjustable and stores keys
- Available accessories enhance versatility



Self-cooling aluminum output tube with mesh guard for safety



Long life heating element with plug-in feature is quick and easy to change



Baffle adjusts air and temperature within range



Plug-in keys are easily interchangeable



Color coded keys each lock in a specific temperature range

Color Key	Model	Temperature Range
Blue	HB1750 B	200 °F - 300 °F
Gray	HB1750 G	300 °F - 500 °F
Yellow	HB1750 Y	500 °F - 750 °F
Orange	HB1750 O	750 °F - 1000 °F
Red	HB1750 R	1000 °F - 1200 °F



Slide switch with cool air stage for rapid cool down

Superior ergonomics and soft-grip handle for fatigue-free operation

Double insulated for safe use with all outlets

Made in E.U. ISO 9001:2000

Specifications

Item No. 34750	Model HB 1750 (Includes all 5 keys)
34751	HB 1750 B Blower w/ Blue key
34752	HB 1750 G Blower w/ Gray key
34753	HB 1750 Y Blower w/ Yellow key
34754	HB 1750 O Blower w/ Orange key
34755	HB 1750 R Blower w/ Red key
Dimensions (h x w x d)	9 1/2" x 5" x 9 1/2"
Weight	2.4 lbs
Voltage	120 VAC / 60 Hz
Output	1750 W
Temperature	200 °F - 1200 °F (all five keys)
Airflow rate	Up to 23 CFM, adjustable with baffle
Power cord	Industrial grade rubber, length: 6 ft.

Accessories



Item No. 07695
1/4" / 7mm Reducer
For pinpoint heat



Item No. 07725
8" / 200mm Spreader
For films and packaging



Item No. 07705
Large Reflector
For shrink tubing up to 50mm diameter



Item No. 07715
Small Reflector
For shrink tubing up to 20 mm diameter