




Eveready Battery Company, Inc.

533 Maryville University Drive
 St. Louis, MO 63141
 Telephone 1-800-383-7323
 Internet: www.energizer.com

Engineering Data

AAA
Alkaline 1.5V
 No Added Mercury or Cadmium

ENERGIZER NO. E92



| Millimeters | Inches |
|-------------|--------|
| 0.10 | 0.004 |
| 0.80 | 0.031 |
| 3.80 | 0.15 |
| 9.50 | 0.374 |
| 10.50 | 0.413 |
| 42.35 | 1.667 |
| 42.85 | 1.687 |
| 43.30 | 1.705 |
| 44.50 | 1.752 |

Chemical System: Zinc-Manganese Dioxide (Zn/MnO₂)

Designation: ANSI-24A, IEC-LR03

Battery Voltage: 1.5 Volts

Average Weight: 11.5 grams (0.4 oz.)

Volume: 3.8 cubic centimeters (0.2 cubic inch)

Average Service capacity (to 0.8 Volts / cell): 1250 mAh


(Rated Capacity at 25 mA continuous drain)

Cell: One No. 3-312 (size "AAA")


Jacket: Plastic Label

Shelf Life: 7 years


Temperature Effects Typical Service to 0.8 Volts




Constant Resistance Discharge Typical Service









Constant Current Discharge Typical Service



ENERGIZER NO. E92



Typical Applications



Important Notice

This data sheet contains information specific to batteries manufactured at time of its publication. Please contact your Energizer representative for most current information. Contents herein do not constitute a warranty.